

Rittal – The System.

Faster – better – everywhere.



VX 5301.245

Side panel, vertically divided

State: 15/02/2026 (Source: ittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.245 - Side panel, vertically divided for VX IT

Side panels, vertically divided, for VX IT



Features

Model No.	VX 5301.245
Benefits	<p>Easy to use</p> <p>Easy to close with snap fasteners</p> <p>Optimum access to all installed components</p> <p>Opening is only possible via internal locking elements, which requires free access via the doors, but significantly increases access security</p> <p>Individual side parts may be completely dismantled at any time without the need for tools</p>
Material	Sheet steel
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	<p>2 side parts</p> <p>Punched rail</p> <p>6 Hinges</p> <p>4 quick-release fasteners</p> <p>Assembly parts</p>
Assembly instruction	Access via the front and rear doors must be guaranteed
To fit	<p>Enclosure type: VX IT</p> <p>Height: = 2,200 mm</p> <p>Depth: = 1,200 mm</p>

Features

IP protection category to IEC 60 529	IP 20
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	35
Gross weight	36.4
PCF per pack (cradle-to-gate)	138.7 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177955868
E-Number Sweden	E7282560
ETIM 9	EC002524
ECLASS 8.0	27182101