### Rittal - The System.

Faster – better – everywhere.





### VX 5301.348

# Gland plate module for side cable entry

State: 16/10/2025 (Source: rittal.com/uk-en)



## VX 5301.348 - Gland plate module for side cable entry for VX IT

With adjustable openings and brush strips on both sides. The version which is open at the side even allows retrospective fitting of the base plate module with the cables already installed.

#### **Features**

Model No.	VX 5301.348	
Product description	With adjustable opening and brush strips on both sides. The version which is open at the side even allows the base plate module to be retro-fitted with the cables already installed.	
Material	Module plate: Sheet steel Brush strip: Plastic, UL 94 HB, halogen-free	
Surface finish	Module plate: Zinc-plated	
Supply includes	Assembly parts	
Assembly instruction	Several gland module plates must be combined to seal the base completely in the VX IT  The gland plate module may be combined in exchange with other base modules with a depth of 237.5 mm.	
Note	Gland plate modules with brush strip not suitable for applications with a protection category to IEC 60 529	
To fit	Enclosure type: VX IT Width: = 800 mm	
Packs of	1 pc(s).	
Net weight	2	
Gross weight	2.36	
PCF per pack (cradle-to-gate)	9 kg CO2 eq (Cat B)	
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared	
Customs tariff number	94039910	
EAN	4028177951006	

© Rittal 2025 2

### **Features**

ETIM 9	EC002620	
ECLASS 8.0	27189261	

© Rittal 2025 3