

Rittal – The System.

Faster – better – everywhere.



DK 5301.446

Aluminium/sheet steel door, vented

State: 1/02/2026 (Source: rittal.com/uk-en)



FRIEDHELM LOH GROUP

DK 5301.446 - Aluminium/sheet steel door, vented for VX IT

To replace existing doors. The vented surface area is approx. 85% perforated.



Features

| | |
|----------------------|---|
| Model No. | DK 5301.446 |
| Product description | To replace existing doors. The vented surface area is approx. 85% perforated. |
| Material | Frame: Extruded aluminium section Vent grille: Sheet steel Vertical extrusion: Aluminium, anodised Horizontal extrusion: Aluminium, spray finished |
| Colour | Comfort handle VX, hinges, horizontal extrusion, vent grille: RAL 9005 Vertical profile: silver coloured |
| Supply includes | Door with comfort handle for semi-cylinders with security lock 3524 E 3 x 180° hinges, fitted Assembly parts |
| Assembly instruction | For a door opening angle of 180° when baying, a 180° baying hinge is required |

Features

| | |
|-------------------------------|--|
| Note | Door opening angle for stand-alone siting: max. 240° Door opening angle when baying: max. 105° |
| To fit | Enclosure type: VX IT Width: = 800 mm Height: = 2,000 mm |
| Packs of | 1 pc(s). |
| Net weight | 10.3 |
| Gross weight | 11.2 |
| PCF per pack (cradle-to-gate) | 42.7 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| EAN | 4028177955059 |
| ETIM 9 | EC000747 |
| ECLASS 8.0 | 27182204 |