

# Rittal – The System.

Faster – better – everywhere.



## DK 5301.450

## Aluminium/sheet steel door, vented

State: 16/05/2024 (Source: [rittal.com/uk-en](https://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5301.450 - Aluminium/sheet steel door, vented for VX IT

To replace existing doors. The vented surface area is approx. 85% perforated.



## Features

Model No.	DK 5301.450
Product description	To replace existing doors. The vented surface area is approx. 85% perforated.
Material	Frame: Extruded aluminium section Vent grille: Sheet steel Vertical extrusion: Aluminium, anodised Horizontal extrusion: Aluminium, spray finished
Colour	Comfort handle VX, hinges, horizontal extrusion, vent grille: RAL 9005 Vertical profile: silver coloured
Supply includes	Door with comfort handle for semi-cylinders with security lock 3524 E 3 x 180° hinges, fitted Assembly parts
Assembly instruction	For a door opening angle of 180° when baying, a 180° baying hinge is required

# Features

Note	Door opening angle for stand-alone siting: max. 240° Door opening angle when baying: max. 105°
To fit	Enclosure type: VX IT Width: = 600 mm Height: = 2,200 mm
Packs of	1 pc(s).
Weight/pack	10.8 kg
EAN	4028177955066
ETIM 7.0	EC000747
ECLASS 8.0	27182204