


# Rittal – The System.

Faster – better – everywhere.



DK 5301.652

Sheet steel door, vertically divided,  
vented

State: 10/02/2026 (Source: [ittal.com/uk-en](http://ittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5301.652 - Sheet steel door, vertically divided, vented for VX IT

To replace existing doors. The vented surface area is approx. 85% perforated.



## Features

Model No.	DK 5301.652
Product description	To replace existing doors. The vented surface area is approx. 85% perforated.
Material	Sheet steel
Surface finish	Spray-finished
Colour	Door: RAL 7035 Comfort handle VX, hinges: RAL 9005
Supply includes	Door, vertically divided, with comfort handle VX for semi-cylinders with security lock 3524 E, right 3 x 180° hinges, fitted on each half of the door Assembly parts
Assembly instruction	For a door opening angle of 180° when baying, a 180° baying hinge is required
Note	Door opening angle for stand-alone siting: max. 240° Door opening angle when baying: max. 160°

# Features

---

IP protection category to IEC 60  
529

---

To fit

Enclosure type: VX IT  
Width: 800 mm  
Height: 2,000 mm

---

Packs of

1 pc(s).

---

Net weight

15

---

Gross weight

15.8

---

Customs tariff number

94039910

---

EAN

4028177955141

---

ETIM 9

EC000747

---

ECLASS 8.0

27182204

---