

# Rittal – The System.

Faster – better – everywhere.



## DK 5528.790

### Network/server enclosure TS IT

State: 1/02/2026 (Source: [ittal.com/uk-en](http://ittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5528.790 - Network/server enclosure TS IT with glazed door, IP 55, empty enclosure

TS IT, sealed, for direct enclosure-specific climate control. Available without 482.6 mm (19") interior installation as an empty enclosure for individual configuration in a range of size variants, and with a protection category of up to IP 55.

## Features

Model No.	DK 5528.790
Material	Sheet steel Aluminium
Surface finish	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder-coated
General colour	RAL 7035
Colour	Enclosure frame and panels: RAL 7035
Supply includes	TS 8 enclosure frame with doors and roof plate Glazed aluminium door at the front (180°) Sheet steel door at the rear, 180° hinges Lock front and rear: Comfort handle for profile half-cylinders and security lock 3524 E Roof plate, one-piece, solid Base tray with gland plate, multi-piece, solid Baying seal and sealing kit for gland plates (supplied loose) Connection accessories for potential equalisation with earthing point (supplied loose) 12 x 482.6 mm (19") fastener, 1 U, conductive (supplied loose) 50 multi-tooth screws, conductive (supplied loose) IPPC pallet
Dimensions	Width: 600 mm Height: 1,800 mm Depth: 800 mm
Design doors	Sealed, IP 55
482.6 mm (19") level(s) version	Without 482.6 mm (19") interior installation

# Features

---

Protection category to IEC 60 529	IP 55 only in conjunction with baying seal or screw-fastened side panels
Note	Depending on how and where it is sited, the door opening angle may vary for selected applications For enclosures with height and depth 2000 x 1200 mm / 2200 x 1000 mm / 2200 x 1200 mm, the matching side panels are optionally available and are supplied fitted to the enclosure
Basic material	Aluminium
Packs of	1 pc(s).
Net weight	73.5
Gross weight	75
EAN	4028177703698
E-Number Sweden	E7239937
ETIM 9	EC002499
ECLASS 8.0	27180207

# Approvals

---

Approvals	UL + C-UL (listed)
Certificates	Surface finish Protection category
Explanations	Declaration of conformity

# Tender text

TS IT 5528.790

TS IT network server enclosure  
for protected siting of components - protection  
category (IP 55)

IT rack with increased protection category, glazed  
door at the front, one-part solid sheet steel door at  
the rear. Empty enclosure without interior  
installation.

Pre-configured IT rack consisting of torsionally  
stiff, welded symmetrical frame of rolled 16-fold  
vertical sections connected with two horizontal frames  
of rolled 9-fold sections with integral channel for  
accommodating the side panel seal and protecting it  
against possible effect of aggressive media.

All frame sections, with integral system punchings on  
a 25 mm DIN pitch pattern, allow convenient interior  
installation by simple fitting and securing of  
equipment. All sections have chamfered edges. The  
vertical frame sections have two depth/width -  
recessed mounting levels each, which can individually  
be used for flexible attachment of the installation  
components.

Enclosures are bayable on all sides: on the left,  
right, front and rear, at the top or round corners.

Glazed front door with viewing panel made from 3 mm  
single-pane safety glass (ESG), framed in a frame of  
aluminium sections, with foamed-in seal,

Sheet steel door, one-part, solid (IP 55) for  
protected siting of components against any poor  
ambient conditions.

Doors with foamed-in seal, four-point locking rod,  
comfort handle for semi-cylinder (30/10) mm, with  
security lock 3524 E. Hinges, with captive hinge pins,  
hinge opening angle with stand-alone siting on both  
sides 180°. Door hinging may be swapped from right to  
left without dismantling locking rods.

One-part solid screw-fastened roof plate with  
all-round foamed-in seal. For supporting the passive  
ventilation it is possible to raise the roof plate

optionally by means of spacers.

Base frame with base tray and multi-piece solid gland plate. Sealing kit for gland plates and baying seal (IP 55) supplied loose.

Pre-configured with two punched sections without mounting flange on the inner mounting level, in the enclosure depth, as shipping brace or as a basis for further population.

All panels have automatic potential equalisation and are prepared for attachment of earthing straps.

482.6 mm (19") assembly parts and complete earthing kit supplied loose.

Supply includes earthing kit and central earth connection.

Side panels are not included with the supply.

One-part screw-fastened variant (IP 55), available from the accessories range or as complete delivery (enclosure incl. screw-fastened side panels).

Material: Sheet steel, aluminium

Surface finish: Panels, doors, RAL 7035

Approvals: IP 55 to IEC 60529

Dimensions (WxHxD): 600x1800x800 mm

Model No.: TS IT 5528.790

Manufacturer: Rittal GmbH & Co. KG