


Rittal – The System.

Faster – better – everywhere.



TE 7000.410

Network racks TE 7000

State: 2/07/2025 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TE 7000.410 - Network racks TE 7000

TE 7000 IT enclosure, prepared for the individual interior installation.

Features

Model No.	TE 7000.410
Benefits	No frame structure Optimum accessibility Readily dismantled and therefore easily installed
Material	Sheet steel Glazed door: Single-pane safety glass, 4 mm
Surface finish	Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated
Colour	RAL 7035
Supply includes	Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Glazed door at the front, incl. 130° hinge, recessed handle and security lock 3524 E Sheet steel door at the rear, including 130° hinge, security lock 3524 E Side panels, lockable, including security lock 3524 E Base frame with maximum cut-out (for optional population with module plates) Roof plate including brush strip for cable entry and concealed cut-out for optional fan. Levelling feet, M10 (supplied loose) Spacers, 20 mm (supplied loose) to raise the roof
Dimensions	Width: 600 mm Height: 600 mm Depth: 800 mm
Units	11 U
Units	11 U
Distance between levels as delivered	495 mm

Features

Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	43
Gross weight	49.5
EAN	4028177460546
ECLASS 8.0	27180207

Tender text

TE 7000 network enclosure, 11 U, W x D 600 x 800 mm

TE 7000 network enclosure

Screw-fastened, dismountable enclosure design based on self-supporting 482.6 mm (19.) mounting angles, which simultaneously form the enclosure frame.

Modular roof and base frames that can be connected together using 482.6 mm (19.) mounting frames to form a supporting enclosure frame. Quick-release, lockable side panels, including 3524 E security lock.

Front glazed door, with 4 mm safety glass, rear steel sheet door. Both include 2-point locking rod, recessed handle, 3524 E security lock, can be exchanged for Ergoform S-handle for integrating a semi-cylinder if required. Door catch position can also be changed; 130° door opening angle.

Roof plate with integrated brush strip; ready to connect up fan-and-filter unit including thermostat control is an optional upgrade.

Two depth adjustable 482.6 mm (19.) mounting frames with integrated 25 mm system punching are used for the internal assembly. The 19. mounting frame is infinitely selectable.

200 kg maximum load capability per mounting level, max. 400 kg for each rack.

The enclosure system is a bayed system. A base/plinth can be fitted as an option.

Supply includes: Enclosure including levelling feet and spacer bolts for raising the roof.

Material: Sheet steel

Dimensions: WxHxD: 600 x 600 x 800 mm

Installation clearance height: 11 U

Protection category: IP 20