

# Rittal – The System.

Faster – better – everywhere.



## VX 7030.265 Doors for VX IT

State: 15/09/2025 (Source: [rittal.com/uk-en](https://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 7030.265 - Doors for VX IT for Automatic Door Opening (ADO)

Glazed and sheet steel doors VX IT, with vent flaps for automatic opening in the event of an alarm



## Features

|           |   |
|-----------|---|
| Model No. | VX 7030.265   |
| Design    | <p>Viewing window: Single-pane safety glass, 3 mm</p> <p>Spring damper for flap opening</p> <p>Magnets for fixing the flaps</p> <p>Valves are open at zero current</p> <p>Glazed door: 2x single-pane safety glass, tinted one-part, with vent flaps</p> <p>Frame: Extruded aluminium section</p>   |
| Benefits  | <p>Supports remote control via the CMC III system</p> <p>Tinted single-pane safety glass ensures a high standard of safety</p> <p>Combining the vent flaps with a tubular door frame creates exceptional stability</p> <p>The vent flaps only protrude into the escape route by 200 mm</p> <p>No adjustment to the lock system required</p> <p>Manually opening the door has no influence on the vent flaps</p> <p>Automatic opening of the vent valves in the event of a power failure</p> |

# Features

|                                     |  |
|-------------------------------------|--|
| Technical specifications            | <p>External projection of the vent flap: 200 mm (when opened)</p> <p>Internal projection of the mechanism: 52.5 mm</p> <p>Door hinge: right (for one-piece doors, may be swapped from right to left)</p> <p>Connection cable from door catch: 2.5 m</p>  |
| Function principle                  | <p>Activation via CMC III door control module (DCM)</p> <p>Automatic, mechanical opening of the integral vertical ventilation flaps in an emergency if the cooling system fails or an extinguishing system is activated</p> <p>Depending on the room volume and temperature, the air inside the room is used for emergency cooling, or the extinguisher gas may flow directly into the IT enclosures</p> <p>The front and rear doors of the ADO system must always be used</p> |
| Material                            | <p>Frame: Extruded aluminium section</p> <p>Viewing panels: Single-pane safety glass, tinted</p>   |
| Supply includes                     | Glazed door with comfort handle for semi-cylinders with security lock 3524 E   |
| With DC                             | 0.78 A   |
| Dimensions                          | <p>Width: 800 mm</p> <p>Height: 2,200 mm</p>   |
| IP protection category to IEC 60529 | IP 20 for solid vent flaps   |
| Packs of                            | 1 pc(s).   |
| Net weight                          | 45   |
| Gross weight                        | 46   |
| Customs tariff number               | 94039910   |
| EAN                                 | 4028177925892  |
| ETIM 9                              | EC000261   |
| ECLASS 8.0                          | 27180101   |