## Rittal – The System.

Faster - better - everywhere.





# IT 7100.120 OCP ORV3 rack


State: 15/11/2025 (Source: rittal.com/uk-en)



#### IT 7100.120 - OCP ORV3 rack

OCP is an ambitious international community that aims to simplify and optimise IT infrastructure. The Rittal OCP ORV3 rack is OCP accepted and ready for immediate use. Simple modifications and enhancements can be made as and when required, thanks to the range of accessories. The OCP ORV3 rack can also accommodate a Direct Liquid Cooling (DLC) solution. Take your efficiency and performance density to a whole new level with this rack.







#### **Features**

Model No.	IT 7100.120
Design	Open frame
	with busbar
	Prepared for cable entry in roof and base
	Cable routing at the front, across the full height
Benefits	Prepared to accommodate 21" OCP components and direct contact on the busbar
	Rapid construction and service thanks to click-in fitting of the IT and
	IT OCP Power rail system
	End-to-end cable management in front rack over full height
	Ideal for high-performance computing and AI technology thanks to
	being ready for Direct Liquid Cooling solutions that are designed to
	dissipate the thermal load generated in the rack
	Integrated heavy-duty castors make transportation easier and
	ensure ease of handling in the data centre
Technical specifications	Rated operating voltage: 48 V DC / power consumption 18 kW
Material	Sheet steel
Surface finish	Dipcoat-primed, powder-coated on the outside
Colour	RAL 9005

© Rittal 2025 2

### Features

OCP ORV3 rack OCP busbar for max. 48 DC/18 kW
2 bracing struts, pre-assembled Levelling feet, pre-assembled 4 castors (freely rotating) Baying seal Air baffle plate
Width: 600 mm Height: 2,286 mm Depth: 1,068 mm
44 OU
14,000 N
Sheet steel
1 pc(s).
172
200
94032080
4028177997738
EC002499
EC002499
27180207

## Approvals

Approvals	IEC CB UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3