### Rittal - The System.

Faster - better - everywhere.





## DK 5501.725 Component shelf, pull-out

State: 8/12/2025 (Source: rittal.com/uk-en)



# DK 5501.725 - Component shelf, pull-out for VX IT, TS IT, TE, TX CableNet

For mounting between two 482.6 mm (19") mounting angles.



#### **Features**

DK 5501.725
For mounting between two 482.6 mm (19") mounting levels, on 482.6 mm (19") mounting angles or 482.6 mm (19") mounting frames.
Tool-free, time-saving one-man assembly from the enclosure front Self-locking Fully extendible
Depth-variable to adapt to individual distances between levels
Sheet steel
Base: Spray-finished Telescopic slides/installation kit: Zinc-plated
RAL 9005
Component shelf, slotted Telescopic slide with mounting kit Assembly parts
100 kg
Width: 419 mm Depth: 700 mm

© Rittal 2025

#### **Features**

To fit	Enclosure type: VX IT TS IT TE
Distance between levels	600 - 900 mm
Packs of	1 pc(s).
Net weight	10.184
Gross weight	10.72
PCF per pack (cradle-to-gate)	40.8 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177679160
E-Number Sweden	E7239597
ETIM 9	EC002620
ECLASS 8.0	27189261

© Rittal 2025 3

#### Tender text

482.6 mm (19") - component shelf, pull-out
482.6 mm component shelf, with telescopic slide, for
L-shaped mounting angles and similar mounting angle
shapes. For mounting between two 482.6 mm (19")
mounting angles. Complete kit including depth-variable
installation kit for 482.6 mm (19") mounting levels
from 600 to 900 mm.

Tool-free, accessory-free, time-saving one-man assembly from the enclosure front.

Locate, pull-out, snap into position.

Perforated component shelf surface to support climate control inside the enclosure. The component shelf is self-locking, fully extendible.

Component shelf depth 700 mm, load capacity 100 kg, component shelf height 1 1/2 U.

Material: Sheet steel

Surface finish: Spray finished

Colour: RAL 9005

Model No. DK: 5501.725

© Rittal 2025 4