
Rittal – The System.

Faster – better – everywhere.





DK 7484.035

Component shelf for frame attachment

State: 30/10/2025 (Source: rittal.com/uk-en)



DK 7484.035 - Component shelf for frame attachment for enclosure widths 600 mm, 800 mm

For installation in enclosures without 482.6 mm (19") accommodation.

Features

Model No.	DK 7484.035
Design	Slotted
Product description	For frame attachment, for installation in enclosures without 482.6 mm (19") accommodation.
Benefits	Mounting bolts or mounting rails may be installed on a 25 mm pitch pattern in the enclosure depth. Mounting hole for handles provided.
Applications	For installation in enclosures without 482.6 mm (19") accommodation
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 7035
Supply includes	Component shelf, slotted 2 mounting rails
Installation options	Static installation: Component shelf, 50 kg with fixing bolts on punched section without mounting flange Static installation: Component shelf, 100 kg with mounting rails on punched sections without mounting flange Depth variable: Component shelf, 50 kg with telescopic slides on punched sections without mounting flange
Load capacity	100 kg area load
Assembly instruction	Additionally, two punched sections with mounting flanges are required for the inner mounting level
Note	Max. depth of component shelves = Enclosure depth - 100 mm.

© Rittal 2025 2

Features

Dimensions	Width: 671 mm
	Height: 45 mm
	Depth: 400 mm
To fit	Enclosure type: VX
	VX IT
	TS IT
	Width: 800 mm
Packs of	1 pc(s).
Net weight	7.111
Gross weight	7.485
PCF per pack (cradle-to-gate)	28.5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177166011
ETIM 9	EC002620
ECLASS 8.0	27189261

© Rittal 2025 3

Tender text

Component shelves for 800 mm wide network enclosures

Component shelves for 800 mm wide network enclosures Version: Max. load capacity 100 kg
Component shelves, W x D = 671 x 400 mm, 2 mm thick steel sheet version; for installing in 800 mm wide network enclosures.

The component shelf is slotted to prevent the accumulation of heat. The component shelves can hold a maximum load of 100 kg.

The height of the fitted component shelves can be adjusted using the 25 mm pitch pattern in network enclosures with a DIN pitch pattern but is infinitely adjustable in network enclosures with aluminium frames.

Material: sheet steel Paint finish: RAL 7035

Dimensions: W x D: 671 x 400 mm

© Rittal 2025 4