

Rittal – The System.

Faster – better – everywhere.



DK 7824.360

Sheet steel door, vertically divided, vented

State: 4/03/2026 (Source: [https://www.rittal.com/uk-en](#))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7824.360 - Sheet steel door, vertically divided, vented for DK-TS

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

Features

Model No.	DK 7824.360
Product description	With 130° hinges and locking rod, including comfort handle for profile half-cylinders with security lock no. 3524 E. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced. The extensive door perforations additionally support climate control of the installed equipment. Perforated surface with air inlet openings > 78%.
Material	Sheet steel
Supply includes	Assembly parts
IP protection category to IEC 60529	IP 20
To fit	Enclosure type: DK-TS Width: 600 mm Height: 2,000 mm
Packs of	1 pc(s).
Net weight	22.6 kg
Gross weight	23.2 kg
Customs tariff number	94032080
ECLASS 8.0	27182204

Tender text

Vertically divided vented sheet steel door,
W x D = 600 x 2000

Sheet steel door with 130° hinges and assembly parts,
locking rod including comfort handle for semi-cylinder
with 3524 E security lock.

Material: Sheet steel, spray finished in RAL 7035
Enclosure W x D: 600 mm x 2000 mm