## Rittal - The System.

Faster - better - everywhere.





# DK 7856.005 PSM busbars

State: 19/11/2025 (Source: rittal.com/uk-en)



#### DK 7856.005 - PSM busbars

One or two infeeds, with on or three phases, redundant after changing the plug-in module's direction of connection. With measurement option in conjunction with the CMC III system.

#### **Features**

DK 7856.005
With 3 m connection cable (connector type CEE/EN 60 309)
The modular system facilitates basic configuration of the racks, thanks to a vertical support rail with single-/3-phase infeed. The various socket modules to supply the active components may be snap-fitted into the support rail. This can even be done whilst the system is operational, because the support section is shock hazard-protected.
Modules may be retrofitted whilst operational.
Each plug-in module picks off a phase on the support rail, either from infeed or from the redundant infeed, depending on the direction of connection.  Depending on the design, single-/3-phase construction with a maximum current of 2 x (3 x 16 A/32 A).  3-phase redundant infeed supported.  The redundant circuit is completely separate from the 3 phases of the support rail.  Modules may be equipped with integral overcurrent protection, so that only the affected module is deactivated in the event of an excessively high current. The other modules remain operational.
Aluminium section, natural anodised
3 m
CEE
1
3~
16 A
7

© Rittal 2025

### **Features**

To fit	Enclosure type: TS 8
	TS IT
	VX IT
	Height: 2,000 mm
Operating temperature range	5 °C45 °C
Ambient humidity (non-	595 %
condensing)	
Storage temperature range	-20 °C60 °C
Packs of	1 pc(s).
Net weight	4.845
Gross weight	5.1
Customs tariff number	85369001
EAN	4028177579200
ETIM 9	EC002762
ECLASS 8.0	27371306

## Approvals

Approvals	IEC CB VDE
Explanations	Declaration of conformity

© Rittal 2025 3

#### Tender text

Power System Module busbar with fixed infeed 3x16 A
The modular system allows basic equipment of each rack
with a vertical busbar and three-phase infeed.
The slots may be used over the entire enclosure
height due to the vertical arrangement.
Up to 7 socket modules may be snapped into the
slots and thanks to the shock-hazard-protected design
of the busbar it is not necessary to equip all slots
with socket modules.

Socket modules are available in various country versions, e.g. IEC 320 C13, earthing pin, F/B, CH, USA, UK. All modules may be mixed in the busbar. 7 socket modules may be inserted per 2 m of bar. Up to 42 C13 slots are available with IEC 320 modules.

Installation via the plug & play system:

The busbar may be installed in the FlexRack(i) without adaptor or may be retrofitted in all Rittal TS/ PS racks by means of the mounting kit DK 7856.011. Power is supplied via a 5-core, 3 m long cable with open end and wire end ferrules. The socket modules may be replaced and retrofitted whilst operational.

#### Technical equipment:

Three-phase construction with max. 3x16 A. Socket modules may be retrofitted whilst the system is operational. Each module optionally with / without integral miniature circuit-breaker.

#### Technical specifications:

Voltage range three-phase 110 V - 400 V AC 50/60 Hz Neutral connector is required Max. power supply 3x16 A Temperature application range: +5° to +45° Humidity application range: 5% to 95% rel. humidity, non-condensing

© Rittal 2025 4

Protection category IP20

H-section made of aluminium

W x H x D [mm]: 60 x 1908 x 60

Make/model: Rittal type: Busbar Power System Module

with fixed infeed DK 7856.005 or equivalent

© Rittal 2025 5