Rittal – The System.

Faster – better – everywhere.





TX 7888.738 Network rack TX CableNet

State: 7/12/2025 (Source: rittal.com/uk-en)



TX 7888.738 - Network rack TX CableNet with vented door

Taking cable management to a new level: The TX CableNet unites many years of expertise in an IT rack which meets every requirement in terms of functionality and quality, prepared for individual interior installation.







Features

Model No.	TX 7888.738
Design	2nd generation
	may be dismantled
	Vented
	with side panels
Benefits	New roof plate concept: Optimised use of the entire enclosure volume with the enclosure cabling plus optional integration of a fan module
	Efficient frame concept for individual configuration
	Side panels, screw-fastened for rapid access
	482.6 mm (19") mounting angles, front and rear, adjustable in the depth
	Dismantling options
	Comprehensive range of accessories for bespoke interior
	configuration

© Rittal 2025

Features

Material Roof: Sheet steel, 1.5 mm Enclosure frame: Sheet steel, 1.5 mm Door: Sheet steel, 1.2 mm 482.6 mm (19') mounting angles: Sheet steel, 2 mm Side panel: Sheet steel, 1.2 mm Surface finish Enclosure frame: Dipcoat-primed Enclosure panels: Dipcoat-primed, powder-coated Colour RAL 7035 Supply includes Rack with vented front door and rear door Enclosure frame, dismantlable, with 482.6 mm (19') mounting angles, front and rear Side panels Screw-fastened roof plate with concealed cable entry on both sides across the entire enclosure depth plus a central, concealed cut-out for easy integration of a fan module. Dimensions Width: 800 mm Height: 2,000 mm Depth: 800 mm Units 42 U Distance between levels as d45 mm delivered 482.6 mm (19') attachment may be dismantled Design with side panels Design doors Vented Rear door design Sheet steel door, one-piece, vented Vented surface area approx. 78 % perforated Load capacity (static) 500 kg Basic material Sheet steel Packs of 1 pc(s). Net weight 104.5		
Enclosure panels: Dipcoat-primed, powder-coated Colour RAL 7035 Supply includes Rack with vented front door and rear door Enclosure frame, dismantlable, with 482.6 mm (19") mounting angles, front and rear Side panels Screw-fastened roof plate with concealed cable entry on both sides across the entire enclosure depth plus a central, concealed cut-out for easy integration of a fan module. Dimensions Width: 800 mm Height: 2,000 mm Depth: 800 mm Units 42 U Distance between levels as delivered 482.6 mm (19") attachment may be dismantled Design with side panels Design doors Vented Rear door design Sheet steel door, one-piece, vented Front door design Sheet steel door, one-piece, vented Vented surface area approx. 78 % perforated Load capacity 5000 N Load capacity (static) 500 kg Basic material Sheet steel Packs of 1 pc(s).	Material	Enclosure frame: Sheet steel, 1.5 mm Door: Sheet steel, 1.2 mm 482.6 mm (19") mounting angles: Sheet steel, 2 mm
Supply includes Rack with vented front door and rear door Enclosure frame, dismantlable, with 482.6 mm (19") mounting angles, front and rear Side panels Screw-fastened roof plate with concealed cable entry on both sides across the entire enclosure depth plus a central, concealed cut-out for easy integration of a fan module. Dimensions Width: 800 mm Height: 2,000 mm Depth: 800 mm Units 42 U Distance between levels as delivered 482.6 mm (19") attachment may be dismantled Design with side panels Design doors Vented Rear door design Sheet steel door, one-piece, vented Front door design Sheet steel door, one-piece, vented Vented surface area approx. 78 % perforated Load capacity 5000 N Load capacity (static) 500 kg Basic material Sheet steel Packs of 1 pc(s).	Surface finish	
Enclosure frame, dismantlable, with 482.6 mm (19") mounting angles, front and rear Side panels Screw-fastened roof plate with concealed cable entry on both sides across the entire enclosure depth plus a central, concealed cut-out for easy integration of a fan module. Dimensions Width: 800 mm Height: 2,000 mm Depth: 800 mm Units 42 U Distance between levels as delivered 482.6 mm (19") attachment may be dismantled Design with side panels Design doors Vented Rear door design Sheet steel door, one-piece, vented Front door design Sheet steel door, one-piece, vented Vented surface area approx. 78 % perforated Load capacity 5000 N Load capacity (static) 500 kg Basic material Sheet steel	Colour	RAL 7035
Height: 2,000 mm Depth: 800 mm Units 42 U Distance between levels as delivered 482.6 mm (19") attachment may be dismantled Design with side panels Design doors Vented Rear door design Sheet steel door, one-piece, vented Front door design Sheet steel door, one-piece, vented Vented surface area approx. 78 % perforated Load capacity 5000 N Load capacity (static) 500 kg Basic material Sheet steel Packs of 1 pc(s).	Supply includes	Enclosure frame, dismantlable, with 482.6 mm (19") mounting angles, front and rear Side panels Screw-fastened roof plate with concealed cable entry on both sides across the entire enclosure depth plus a central, concealed cut-out
Distance between levels as delivered 482.6 mm (19") attachment may be dismantled Design with side panels Design doors Vented Rear door design Sheet steel door, one-piece, vented Front door design Sheet steel door, one-piece, vented Vented surface area approx. 78 % perforated Load capacity 5000 N Load capacity (static) 500 kg Basic material Sheet steel Packs of 1 pc(s).	Dimensions	Height: 2,000 mm
delivered 482.6 mm (19") attachment may be dismantled Design with side panels Design doors Vented Rear door design Sheet steel door, one-piece, vented Front door design Sheet steel door, one-piece, vented Vented surface area approx. 78 % perforated Load capacity 5000 N Load capacity (static) 500 kg Basic material Sheet steel Packs of 1 pc(s).	Units	42 U
Design with side panels Design doors Vented Rear door design Sheet steel door, one-piece, vented Front door design Sheet steel door, one-piece, vented Vented surface area approx. 78 % perforated Load capacity 5000 N Load capacity (static) 500 kg Basic material Sheet steel Packs of 1 pc(s).		445 mm
Design doors Vented Rear door design Sheet steel door, one-piece, vented Front door design Sheet steel door, one-piece, vented Vented surface area approx. 78 % perforated Load capacity 5000 N Load capacity (static) 500 kg Basic material Sheet steel Packs of 1 pc(s).	482.6 mm (19") attachment	may be dismantled
Rear door design Sheet steel door, one-piece, vented Front door design Sheet steel door, one-piece, vented Vented surface area approx. 78 % perforated Load capacity 5000 N Load capacity (static) 500 kg Basic material Sheet steel Packs of 1 pc(s).	Design	with side panels
Front door design Sheet steel door, one-piece, vented Vented surface area approx. 78 % perforated Load capacity 5000 N Load capacity (static) 500 kg Basic material Sheet steel Packs of 1 pc(s).	Design doors	Vented
Vented surface area approx. 78 % perforated Load capacity 5000 N Load capacity (static) 500 kg Basic material Sheet steel Packs of 1 pc(s).	Rear door design	Sheet steel door, one-piece, vented
Load capacity (static) 500 kg Basic material Sheet steel Packs of 1 pc(s).	Front door design	•
Basic material Sheet steel Packs of 1 pc(s).	Load capacity	5000 N
Packs of 1 pc(s).	Load capacity (static)	500 kg
	Basic material	Sheet steel
Net weight 104.5	Packs of	1 pc(s).
	Net weight	104.5

© Rittal 2025 3

Features

Gross weight	114.5
Customs tariff number	94039910
EAN	4028177997547
ETIM 9	EC002499
ETIM 8	EC002499
ECLASS 8.0	27180207

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025

Tender text

IT rack, installation height 42 U, vented door at the front, readily dismantled, One-piece vented door at the rear. Article number 7888.738

Frame structure:

IT rack, consisting of a torsion-resistant, welded, symmetrical frame made of rolled and 16-folded vertical profiles, connected to a horizontal frame below and horizontal cross profiles, with screwed roof plate at the top. All frame profiles, with integrated system perforation in a 25 mm hole grid, enable convenient interior design by simply hanging and securing the installation components. All profile edges are rounded. The vertical frame profiles each have two in depth and width staggered mounting levels, which can be individually adjusted for flexible fastening of the components. The baying of the cabinets is possible at the front, back and side. Load capacity: up to 500 kg.

Floor:

Open floor frame, without floor panels, optionally for individual equipping with floor modules from the accessories range.

Front and back door:

Sheet steel door, one-piece, ventilated front and rear, with 78% ventilation area. Front and rear doors each double hinged, with designer handle and 2-point bar lock, Safety lock 3524 E, replaceable with AX comfort handle

Optional integration of a semi-cylinder. Swapping door hinge side possible, door opening angle 135° when installed individually, 105° in array. Door hinges with captive hinge pins.

Roof sheet:

Sheet steel roof, one-piece, closed, screwed, prepared for cable routing on the side, prepared in the middle for fan installation with up to 6 fan units. Roof plate can be rotated for cable routing at the front and rear. To support passive ventilation

the roof sheet can optionally be raised using spacers.

Mounting levels:

Cabinet pre-assembled with two 482.6 mm (19") mounting levels, front and rear. The total static load capacity of both assembly levels is 500 kg. Mounting levels consisting of universal profile rails, front and rear, variable in width and depth, in 15 mm dimensions, on depth struts at the top and bottom

in the cabinet frame, screwed. The 19" mounting levels can't be

© Rittal 2025 5

positioned with offset inside the housing.

Profile rails at the front and back, included additional hole pattern according to standard EIA 310 E. All height units marked on the profile rails and numbered bidirectionally. Unit marking on both mounting levels for simplified assembly of the installation components can be read from the front outside and the back inside.

Profile rails at the front prepared for tool-free mounting of cable management aids for organizing structured cabling within highest packing density. Profile rails at the rear prepared to accommodate a Power Distribution Unit (PDU) on both sides with the 1U form factor, without consumption of installation volume due to the special space-saving lateral installation between the mounting level and the side wall within

Zero U Space.

Side walls:

One-piece screwed side walls mounted on the cabinet.

Material:

Cabinet frame, roof: sheet steel 1.5 mm

Roof cutouts: 1.2mm

Rear door: sheet steel 1.2 mm Front door: sheet steel 1.2 mm 19" profile rails: sheet steel 2.0 mm

Surface:

Flat parts, doors dip-primed, powder-coated in RAL 7035

Interior installation dip primed in RAL 9005

Cabinet frame dip primed in RAL 7035

Approvals:

CE declaration of conformity

RoHS 3

Dimensions (WHD): 800x2000x800 mm

Item number: 7888.738

Manufacturer: Rittal GmbH & Co. KG

© Rittal 2025 6