Rittal - The System.

Faster – better – everywhere.





DK 7111.214

Cable routing bars, 482.6 mm (19") attachment

State: 29/10/2025 (Source: rittal.com/uk-en)



DK 7111.214 - Cable routing bars, 482.6 mm (19") attachment

For structured routing of entire cable bundles, 482.6 mm (19") attachment, connection comb.







Features

Model No.	DK 7111.214
Product description	For structured routing of entire cable bundles, the cable bars may be secured to a variety of different positions inside the enclosure.
Applications	For horizontal cable routing within the distributor level. Thanks to their open mounting holes, they can also be retrospectively slotted onto the 482.6 mm (19") system punchings of the mounting level at any time and secured with the existing mounting screws of the installed components.
Material	Support: Sheet steel Cable routing bars, connection combs: Plastic UL 94-V0
Colour	RAL 9005
Supply includes	Cable routing bars Connection combs
Number connection combs	5
Note	Size of individual chambers (WxD) approx. 34 x 100 mm
Units	1 U
Packs of	10 pc(s).

© Rittal 2025

Features

Net weight	0.57
Gross weight	0.668
PCF per pack (cradle-to-gate)	2.6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177550360
E-Number Sweden	E7282517
ETIM 9	EC000322
ECLASS 8.0	27400604

© Rittal 2025 3

Tender text

Cable bracket for 482.6mm (19") system punchings, 1 U

1 U single bracket element for horizontal cable guiding directly on the 482.6mm (19") distribution level. The bracket elements allow themselves to be slid back on the 482.6mm (19") system punchings through their open mounting holes at any time and to be fixed with the available securing screws of the mounting components. An extension of existing units through baying by means of connecting piece is possible. For this the connecting piece is put between two bracket elements and thus connects the elements by forming an additional guide chamber between the bracket elements. The connecting pieces needed for baying are contained within the units. delivery scope. The single bracket has a height of approx one height unit (44.45 mm) and thus enables the U related cable feed of whole cable bunches.

Each individual cable bracket can be opened selectively and independently of the others and closed again by means of a turning catch. It thus enables straightforward structuring of the cabling and also flexible change to it

Support element sheet steel, spray finished Cable feed brackets, connecting pieces, turning catches, plastic

© Rittal 2025 4