# Rittal - The System.

Faster – better – everywhere.





State: 9/12/2025 (Source: rittal.com/uk-en)



# DK 7320.721 - Handles, electromagnetic for CMC III and IoT Interface

Handles may be integrated into various enclosure systems.

## **Features**

Model No.	DK 7320.721
Design	Comfort handle:with master key function
Product description	For control and monitoring via a central CMC III type control unit and loT interface.
Colour	RAL 7035
Supply includes	2 adaptors for glazed door
	Cable clamps
	Adaptor for profile half-cylinders
	Connection cable (3 m) with RJ 12 connector
	Assembly parts
Lock type	Master key function (with emergency open function)
Rated current max.	0.1 A
No. of participants per IoT interface (max.)	16
No. of participating PU compact (max.)	2
No. of participating PU (max.)	16
Number subscribers per PDU note	Max. 5 p. for power supply with PoE
Packs of	1 pc(s).
Net weight	0.99
Gross weight	0.992
Customs tariff number	83024110
EAN	4028177390386
ETIM 9	EC000327

© Rittal 2025

#### **Features**

ECLASS 8.0

27409217

## **Approvals**

**Explanations** 

Manufacturer's declaration Declaration of conformity

#### Tender text

Comfort handle for TS 8 with master-key function, The TS 8 handle includes the master key function. This means that, independently of the control system, the handle can always be opened using the master-key. The door can be released via the CMC-TC system. In addition an access unit (V1.1) and an access sensor (7320.530) should be used so that the door status can be polled.

Technical specifications:

Rated voltage: 24 V DC

Rated current: max. 100 mA

Connection cable: Length 3 m, RJ 12 connector

Connection cable: Length 2 m, RJ 12/RJ 12 connector

Extension coupling: RJ 12/RJ 12 jack

Temperature application range: +5°C to +40°C

Protection category: IP 40

3