


Rittal – The System.

Faster – better – everywhere.



DK 7507.000 FlatBox

State: 27/06/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7507.000 - FlatBox

Flat-packed enclosure. For optimum access and flexible use as a wall-mounted or floor-standing enclosure.



Features

| | |
|---------------------|--|
| Model No. | DK 7507.000 |
| Design | with 482.6 mm (19") mounting angles |
| Product description | For flexible use as a wall-mounted or floor-standing enclosure. |
| Benefits | Tool-free quick assembly System assembly on the open 482.6 mm (19") frame |
| Material | Sheet steel Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Colour | RAL 7035 |
| Supply includes | Flat-packed enclosure 1 wall section 2 basic supports 2 roof/base plates, with cut-outs for cable entry via brush strips 2 side panels, lockable 1 glazed door, lockable, security lock 3524 E, door hinge point selectable Connection components for tool-free, fast assembly Earthing kit for system-compatible earthing of all enclosure parts 482.6 mm (19") mounting angles |

Features

| | |
|------------------------------------|---|
| Units | 6 U |
| Dimensions | Width: 600 mm Height: 358 mm Depth: 400 mm |
| Installation height for components | 6 U |
| Load capacity | max. 300 N |
| Note | Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 482.6 mm (19") levels: Depth - 104 mm The maximum door opening angle is 210° |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Net weight | 16.739 kg |
| Gross weight | 17.66 kg |
| PCF per pack (cradle-to-gate) | 68 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC002500 |
| ETIM 8 | EC002500 |
| ECLASS 8.0 | 27180208 |
| Product description | DK FlatBox, WHD: 600x358x400 mm, 6 U, with 482.6 mm (19") mounting angles |

Approvals

| | |
|--------------|----------------------------|
| Explanations | Manufacturer's declaration |
|--------------|----------------------------|

Tender text

6 U IT-wall-/standing enclosure in flat pack form
tool free assembly

6 U wall-/standing enclosure with depth adjustable
482.6mm (19") mounting level at front in the 25mm
pitch pattern, consisting of wall part, two carrying
bars, roof and gland plate, each with cut out for
feeding cable, covered with brush strips, two 482.6mm
(19") mounting angles, two lockable side panels and a
lockable glazed door. The enclosure is built up with
snap connecting elements without tools. The
symmetrical basic construction makes a build free of
confusion possible. Freely selectable doorstop.

Static load capacity of the 482.6mm (19") level:

5 kg/U. Roof and base frame and side panels each with
two ventilation fields for passive ventilation, an
extension to active air conditioning is possible with
fan motors which can be obtained separately,
ventilation fields which are not required can be
closed with cover plates which may be obtained
separately. Side panels of variant 7507.000 with only one air outlet
aperture on each side. Use in the form of a standing enclosure
is possible with levelling feet which may be obtained
separately. Additional rear 482.6mm (19") mounting
level possible with horizontal rail sets which may be
obtained separately.

Material:

Sheet steel, glazed door with pane made of single
pane safety glass

Surface finish:

Powder-coated in RAL 7035

Dimensions (W x H x D):

600 x 358 x 400 mm, 6 U