

**Rittal – The System.**

Faster – better – everywhere.



**TS 8612.080**

**TS punched section with mounting  
flange, 17 x 73 mm**

State: 30/06/2025 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8612.080 - TS punched section with mounting flange, 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.



## Features

Model No.	TS 8612.080
Design	For the inner mounting level and for mounting on doors
Product description	For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Length	790 mm
To fit door width	900 mm
Installation options	<p>On the vertical TS, VX SE enclosure section: On the inner mounting level, height-offset all-round</p> <p>For SE, may additionally be mounted on the top horizontal section in the depth</p> <p>In the tubular door frame for TS, SE and PC</p> <p>In TP via rail for interior installation: In the width, for inner mounting level</p> <p>As a mounting kit for component shelves in TS, VX SE, simply locate and secure</p>
Assembly instruction	The rail for internal mounting is required when installing in TP

# Features

---

To fit	Enclosure type: VX SE TP PC IW TX CableNet To fit width/depth: 800 mm
Packs of	4 pc(s).
Net weight	3.384
Gross weight	3.54
PCF per pack (cradle-to-gate)	13.7 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177212107
ETIM 9	EC002625
ECLASS 8.0	27189234

---