

# Rittal – The System.

Faster – better – everywhere.



## DK 7979.204 PDU metered

State: 17/04/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7979.204 - PDU metered

High-end IT rack power distribution: Smart PDU with energy measurement per phase, i.e. output requirement of an entire IT rack



## Features

Model No.	DK 7979.204
Design	482.6 mm (19") version
Product description	High-end power distribution in a compact design for IT network and server racks. With power measurement at the infeed or per phase.
Benefits	<ul style="list-style-type: none"><li>For vertical mounting, it may be attached in the zero-U space of the Rittal VX IT or TS IT rack with no need for tools</li><li>Colour coding of phases and fuse circuits (L1=pink, L2=black, L3=white)</li><li>Tool-free divider kit for VX IT</li><li>PDU self-supplied, no external power supply required</li><li>Measurement accuracy <math>\pm 1\%</math> (kWh) to EN 62 053-21</li><li>Integral real-time clock with battery buffering (max. 10 years, battery replaceable)</li><li>Integral electromagnetic buzzer for acoustic alarms</li><li>Adjustable limit values (warning/alarm) for voltage, current, output</li><li>Operating hours meter, total and cyclical, resettable</li><li>Power-saving design, minimal intrinsic power consumption</li></ul>

# Features

---

Technical specifications	Display/controller unit in the PDU enclosure rotatable through 180° and replaceable Compact circuit-breaker (16 A - Carling type) Integral, fully-redundant power pack, power supply from all phases Error-tolerant PDU power supply redundant across all phases Voltage V, current A, frequency Hz Active power, active energy, apparent power, apparent energy Power factor (cosPhi) and phase angle Zero conductor current measurement/load imbalance detection Fuse monitoring for PDUs with integral fuse Bright TFT display, 128 x 128 pixels (RGB) with back-lighting and energy-saving mode to display output data and basic PDU configuration Position sensors for display rotation and correct PDU representation on the website Power LED to indicate voltage
Material	Aluminium section, black anodised Slots: Plastic
Supply includes	Assembly parts
Options	CMC III CAN bus sensors may be connected for ambient monitoring, max. 16 sensors
Measurement functions, description	Measurement per phase or infeed Powerful CPU (ARM Cortex A8) Digital input (floating contact) Additional alarm output/relay output (changeover contact)
Dimensions	Height: 44 mm Depth: 144 mm Length: 450 mm
No. of sockets and type	4 x C13 / 2 x C19
Rated operating voltage	230 V (AC)
Rated current (max.)	32 A
Power consumption	7.4 kW
Infeeds	Qty.: 1 Phases per infeed: 1~
Length of connection cable	3 m

---

# Features

Type of electrical connection	CEE
Interfaces	USB 2.0 port (USB-A) for mass configuration, firmware updates & data logging CAN bus interface (RJ 45) for a maximum of 16 ambient sensors Serial interface RS232 (RJ12) for LTE unit, scripting, CLI Use of own certificates/TLS 1.2 E-mail forwarding in case of alarm (SMTP) User administration including rights management LDAP(S)/Radius/Active Directory connection Syslog server connection (max. 2 servers) Fully redundant Ethernet interface 10/100/1000 Mbit/s
Number RJ45 ports for sensor units max	2
Directives	EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU
Standards	EN 62368-1 EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21
Protocols	Web server (HTTP, HTTPS, SSL) SSH, Telnet, NTP TCP/IP v4 & v6, DHCP, DNS SNMP v1, v2c & v3, Modbus/TCP, OPC-UA MIB for linking into 3rd party DCIM software FTP/SFTP (update/file transfer)
Operating temperature range	5 °C...50 °C
Ambient humidity (non-condensing)	10...95 %
Storage temperature range	-20 °C...70 °C
To fit	Enclosure type: VX IT enclosure frame: ≥ 800 mm Enclosure type: VX IT 19" mounting angles: ≥ 800 mm
Packs of	1 pc(s).
Net weight	3.38 kg
Gross weight	3.68 kg

# Features

---

Customs tariff number	85366990
ETIM 9	EC002762
ETIM 8	EC002762
ECLASS 8.0	27142604
Product description	DK PDU metered, compact basic power distribution incl. energy measurement per phase, with network interface and display, WHD: 450x44x144 mm, IEC 60320: 4 x C13, 2 x C19

# Approvals

---

Approvals	TÜV
Explanations	Declaration of conformity

# Tender text

Compact power distributor for deployment in IT server and network enclosures. Robust aluminium housing with permanently mounted output slots, IEC 60320/C13 or IEC 60320/C19 as well as CEE 7/3 (earthing-pin) and BS 1363 (UK), depending on the type (see below for details). The IEC C13 / C19 output slots can be protected with a lock against unintentional removal of the connectors. Unused slots can be closed with slot covers available as accessories. This precludes an unintentional overloading of individual phases and circuits. The fuse circuits and phases are colour-coded for multiphase PDU variants. A connection cable with IEC C20 or CEE connector appropriate for the variant makes the PDU available for immediate deployment.

The PDU metered has extensive measurement functions for the current and power monitoring of each phase. The integral TFT colour display enables the basic configuration setting and quick access of the electrical consumption data. Two Gigabit network interfaces and the integrated Web server allow access and data transmission using various protocols. The consumption parameters can be forwarded to a DCIM software via SNMP, OPC-UA, Modbus/TCP. For monitoring the ambient parameters, up to 16 sensors (for example temperature / humidity / smoke / leakage / access) as well as VX IT and TS IT handle systems from the CMC accessories program can be connected to the CAN sensor interface.

Technical specifications metered

Input voltage range (L/N/PE): 230 VAC, 50-60Hz

input current: 32A

No. of phases: 1

Marking of phases (3-phase PDU only L1, L2, L3):

Rittal Power Pink, black, white

Number of slots type IEC 60320/C13 (total): 4

Number of slots type IEC 60320/C13

(per phase/fuse): 4 / 2

Number of slots type IEC 60320/C19 (total): 2

Number of slots type IEC 60320/C19  
(per phase/fuse): 2 /1  
Number of slots type CEE 7/3 (total): -  
Number of slots type CEE 7/3  
(per phase/fuse): -  
No. of circuit breakers: 2  
Hydraulic-magnetic protective circuit-breaker: 16 A  
Connector PDU input:  
EN 60309 / CEE (L+N+PE, 6h)  
Length of connection cable: 3m  
Connection cable type: H05-VV  
No. of wires: 3  
Cable cross-section: 4 mm<sup>2</sup>  
PDU housing width: 450mm  
PDU housing depth: 144mm  
PDU housing height: 44mm (1HU)  
PDU material: Aluminium, anodised, in RAL 9005 (black)<(,<)>  
other colours available on request  
PDU mounting adaptor (VX IT / TS IT) –Mounting options:  
Frame + Zero-U space + cable route  
Measurement functions: Measurement per phase or infeed  
Values recorded (per phase):  
Voltage (V), current (A), frequency (Hz), Power factor<(,<)>  
Active power (kW), active energy (kWh)<(,<)>  
apparent power (kVA)  
Active power(kW),neutral conductor current measurement<(,<)>  
fuse monitoring (at 32 A)  
Optional: Residual current monitoring (RCM)  
AC + DC (RCM Typ B)  
max. 6 measurement points per PDU possible  
(input / per phase / per fuse)  
0 mA – 100 mA je RCM  
Voltage measuring range: 90V - 255V  
Voltage resolution 0.1V  
Current measuring range 0 - 16A/32A  
Current resolution 0.1A  
Measuring accuracy typ. ± 1% according to IEC/EN 62 053-21  
Freely adjustable limit values (warning/alarm) for  
for voltage, current, power: Yes  
Operating hours counter: Yes  
Controllerboard: can be rotated  
and replaced during operation

Display: TFT, RGB 128x128 pixels  
Network interface: 2x RJ45, per 10/100/1000 MBit/s  
Supported protocols:  
IPv4 / IPv6, integral web server  
HTTP, HTTPS, SSL, SSH, NTP, Telnet  
TCP/IP v4 and v6, DHCP, DNS, NTP, Syslog  
SNMP v1, v2c und v3, Traps(>,<)>  
FTP/SFTP (update/file transfer)  
OPC-UA, Modbus/TCP(>,<)>  
FTP/SFTP (update/file transfer>(>,<)>  
E-mail forwarding (SMTP)  
User administration including rights management: Yes  
LDAP(S)/Radius/Active Directory connection: Yes  
USB port for firmware update+data logging functions: Yes  
CAN bus interface: RJ45, for connecting 16 sensors  
CAN sensor types: Temperature(>,<)>  
temperature/humidity (combined),infrared access sensor(>,<)>  
leakage, NH measurement module, smoke alarm, vandalism(>,<)>  
airflow, EFD, differential pressure(>,<)>  
VX IT / TS IT handle system  
Plug & play drivers-Rittal RiZone DCIM software: Yes  
Digital input: 1  
Alarm relay: 48 V DC/2 A  
Acoustic signal encoder  
Serial interface  
Conformity: CE  
Standards:  
Safety: EN 62368  
EMV:  
EN 55022 / B  
EN 61000-4-2  
EN 61000-4-3  
EN 61000-6-2  
EN 61000-6-3  
Safety Directive: 2014/35/EU  
EMC Directive: 2014/30/EU  
MTBF (at 40°C) 100.000 hours  
Protection category: IP 20 (EN 60529)  
Protection class: Class 1  
Pollution degree: 2  
Overvoltage category: II  
Environmental properties: 2011/65/EU (RoHS 2), WEEE

Storage temperature: -20 °C to +70 °C

Ambient temperature: +5°C to +50°C

Ambient humidity 10 - 95% rel. humidity, non-condensing

Operating altitude (max. above mean sea level): 3000 m

Connector lock for C14 and C20 connectors:

1x (further connector locks optional - DK 7979.020)

Covers C13 (optional accessory): DK 7955.010

Covers C19 (optional accessory): DK 7955.015

Type: Rittal PDU metered, Model No.: DK 7979.204