

Rittal – The System.

Faster – better – everywhere.



VX 8619.400 Cable clamp rail

State: 13/04/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.400 - Cable clamp rail Right-angle section for VX, TS, VX SE, PC, base/plinth system VX

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

Features

Model No.	VX 8619.400
Product description	For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
VX installation options	In enclosure width 400 mm, in the base
AX installation options	In enclosure width 400 mm, in conjunction with rail for interior installation AX and base configuration rail for AX
AX stainless steel installation options	In enclosure width 400 mm, in conjunction with rail for interior installation AX and base configuration rail for AX
VX base/plinth installation options	In base/plinth width/depth 400 mm, in conjunction with holder/spacer
To fit	Base/plinth system VX
Dimensions	Length: 354 mm
To fit	Enclosure type: VX AX Width: = 400 mm
Suitable for width	400 mm
Packs of	2 pc(s).
Net weight	2 kg
Gross weight	2.34 kg

Features

Customs tariff number	83024900
ETIM 9	EC000322
ECLASS 8.0	27400604
Product description	VX Cable clamp rail, mounting angle, for W: 400 mm
