Rittal – The System.

Faster – better – everywhere.



VX 8660.021

Base/plinth corner pieces with base/plinth trim panels, front and rear

State: 19/11/2026 (Source: www.rittal.com/uk-en)

VX 8660.021 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, sheet steel

Base/plinth corner pieces with trim panels for flexible cable entry.





Features

Model No.	VX 8660.021
Benefits	Reliable – Excellent stability of the base/plinth Flexible – Countless interior installation options with VX accessories Simple – Flush termination between the baying points
Material	Base/plinth corner piece: Sheet steel Base/plinth trim panel front/rear: Sheet steel Corner and baying cover: Plastic
Colour	RAL 9005
Supply includes	4 corner covers Assembly parts 4 base/plinth corner pieces, 200 mm high 1 base/plinth trim panel, front/rear, 200 mm high 2 base/plinth trim panels, front/rear, 100 mm high
Note	Side base/plinth trim panels finish off a base/plinth unit or provide additional stabilisation between base/plinths or enable interior configuration of the base/plinth

© Rittal 2026

Features

Dimensions	Height: 200 mm
To fit	Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Width: = 400 mm
Type rating to 508A	Type 1 Type 12
Weight/pack	5.85 kg
Packs of	2 pc(s).
Net weight	5.846 kg
Gross weight	5.85 kg
PCF per pack (cradle-to-gate)	22.05 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003
Product description	VX base/plinth corner piece with trim panel, front and rear, H: 200 mm, for W: 400 mm, sheet steel

Approvals

Approvals	UL + C-UL - FTTA

Approvals

Explanations	PCF-declaration