


Rittal – The System.

Faster – better – everywhere.



VX 8619.430 Cable clamp rail

State: 23/05/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.430 - Cable clamp rail Right-angle section for VX, TS, VX SE, PC, base/plinth system VX

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

Features

Model No.	VX 8619.430
Product description	For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
VX installation options	In enclosure width 1000 mm, in the base
VX SE installation options	In enclosure width 1000 mm, in the base
AX installation options	In enclosure width 1000 mm, in conjunction with the AX interior installation rail and AX base configuration rail
AX stainless steel installation options	In enclosure width 1000 mm
VX base/plinth installation options	In base/plinth width/depth 1000 mm, in conjunction with holder/spacer
Installation options for VX base/plinth, stainless steel	In base/plinth width 1000 mm, in conjunction with one M8 nut
AX base/plinth installation options	In base/plinth width 1000 mm
To fit	Base/plinth system AX Base/plinth system VX VX base/plinth system, stainless steel
Dimensions	Length: 954 mm

Features

To fit	Enclosure type: VX VX SE AX CX one-piece console Width: = 1,000 mm
Suitable for width	1,000 mm
Packs of	2 pc(s).
Net weight	5 kg
Gross weight	5.14 kg
Customs tariff number	73269098
ETIM 9	EC000322
ECLASS 8.0	27400604
Product description	VX Cable clamp rail, mounting angle, for W: 1000 mm