## Rittal – The System.

Faster – better – everywhere.





## VX 8619.460 Cable clamp rail

State: 7/12/2025 (Source: rittal.com/uk-en)



## VX 8619.460 - Cable clamp rail Right-angle section for VX, TS, VX SE, PC, base/plinth system VX

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

## **Features**

Model No.	VX 8619.460
Product description	For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
VX SE installation options	In enclosure width 1800 mm, in the base
VX base/plinth installation options	In base/plinth width 1800 mm, in conjunction with holder/spacer
To fit	Base/plinth system VX
Dimensions	Length: 1,754 mm
To fit	Enclosure type: VX SE Width: = 1,800 mm
Suitable for width	1,800 mm
Packs of	2 pc(s).
Net weight	7.7
Gross weight	9.38
Customs tariff number	73269098
EAN	4028177921986
ETIM 9	EC000322
ECLASS 8.0	27400604

© Rittal 2025 2