
Rittal – The System.

Faster – better – everywhere.



VX 8660.035

Base/plinth trim panels, side

State: 19/11/2026 (Source: www.rittal.com/uk-en)


ENCLOSURES POWER DISTRIBUTION CLIMATE CONTROL IT INFRASTRUCTURE SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 8660.035 - Base/plinth trim panels, side for base/plinth system VX, sheet steel

To finish off a base/plinth unit at the sides and for additional stability or interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.





Features

Model No.	VX 8660.035
Design	Solid
Material	Sheet steel
Colour	RAL 9005
Supply includes	Assembly parts
Dimensions	Height: 100 mm
To fit	Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Depth: = 1,000 mm

© Rittal 2026

Features

Type rating to 508A	Type 1 Type 12
Weight/pack	3.67 kg
Packs of	2 pc(s).
To fit	for base/plinth system VX, sheet steel
Net weight	3.4 kg
Gross weight	3.671 kg
PCF per pack (cradle-to-gate)	12.55 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003
Product description	VX base/plinth trim panel, side, H: 100 mm, for D: 1000 mm, sheet steel

Approvals

Explanations	PCF-declaration