

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.650 OM adaptors

State: 3/07/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.650 - OM adaptors with spring terminals



## Features

|   |  |
|---|--|
| Model No.                                     | SV 9340.650  |
| Design  | with spring terminals  |
| Material                                      | Polyamide<br>Fire protection corresponding to UL 94-V0   |
| Colour  | Chassis: RAL 7035  |
| Rated current max.                            | 65 A   |
| Rated operating voltage                       | 690 V, 3~  |
| For bar systems with centre-to-centre spacing | 60 mm  |
| Support rail type                             | Support frame, 1 x TS 55E, 1 x TS 55D-V  |
| Number of poles                               | 3-pole   |
| Support frame support                         | Yes  |
| Note on Model No.                             | According to a heat dissipation test to IEC 61 439-1, a current carrying capacity of up to 80 A is supported |
| Dimensions                                    | Width: 55 mm<br>Height: 272 mm   |
| Connection of round conductors                | 2.5 - 16 mm <sup>2</sup>   |
| Support rails Qty/height                      | 2 / 10 mm  |
| To fit busbars                                | Height: 5, 10 mm   |

# Features

---

|                              |   |
|------------------------------|---|
| Support frame (W x H)        | 55 mm x 237 mm  |
| Packs of                     | 1 pc(s).  |
| Net weight                   | 0.339 kg  |
| Gross weight                 | 0.377 kg  |
| Copper weight (kg per piece) | 0.059   |
| Customs tariff number        | 85369095  |
| ETIM 9                       | EC001531  |
| ECLASS 8.0                   | 27370304  |
| Product description          | SV OM adaptor, 65 A, 690 V, 3-pole, tension spring clamp 2,5-16 mm <sup>2</sup> , WH: 55x272 mm, support frame, support rail TS 55E, TS 55D-V |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | ABS<br>DNV<br>Lloyds Register                             |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

# Tender text

OM adaptor 65 A

OM adaptor 65 A with tension spring clamp, 3-pole,  
for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Construction width: 55 mm

Length: 208 mm

Support frame: 55 x 237 mm

Support frame support: yes

Support rail: 2 with anti-slip guard

System:

Rittal RiLine60