Rittal – The System.

Faster – better – everywhere.



# PK 9518.000


# Polycarbonate enclosures PK

State: 19/11/2026 (Source: www.rittal.com/uk-en)

# PK 9518.000 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.





## Features

| | |
|---|---|
| Model No. | PK 9518.000 |
| Design | PK enclosure with solid cover |
| Product description | Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment. |
| Material | Enclosure: Fibreglass-reinforced polycarbonate<br>Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal<br>Cover screws: Polyamide<br>Insulating bungs: Polyethylene |
| Colour | RAL 7035 |
| Supply includes | Enclosure with cover<br>Cover screws<br>Insulating bungs for wall mounting screws |
| Dimensions | Width: 182 mm<br>Height: 180 mm<br>Depth: 111 mm |

© Rittal 2026

# Features

| | |
|---|---|
| Protection category to IEC 60 529 | IP 66 |
| Protection category NEMA | NEMA 4X |
| IK Code | IK08 |
| Operating temperature range | -35 °C...80 °C |
| Basic material | Polycarbonate |
| Packs of | 1 pc(s). |
| Net weight | 0.641 kg |
| Gross weight | 0.76 kg |
| Customs tariff number | 84879090 |
| ETIM 9 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | PK Polycarbonate enclosure, WHD: 182x180x111 mm, fibreglass-reinforced polycarbonate, without knockouts, with grey cover |

# Approvals

| | |
|---|---|
| Approvals | C-UL<br>DNV<br>UL |
| Explanations | Declaration of conformity |

# Tender text

Polycarbonate Housings without knockouts

Polycarbonate enclosure with solid cover without knockouts
Enclosure: Fibreglass-reinforced polycarbonate
without knockouts for cable entry
Cover: Fibreglass-reinforced polycarbonate

all-round foamed-in PU seal
Cover screws: Polyamide
Insulating bungs: Polyethylene
Supply includes: Cover screws
Insulating bungs for wall mounting screws
Accessories: Wall mounting bracket
Protection category to IEC 60 529: IP 66
Protection category NEMA: NEMA 4X
Colour: similar to RAL 7035
Dimensions (W x H x T): 182 x 180 x 111 mm