

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.600

## RiLineX CB component adaptor

State: 9/09/2025 (Source: [rittal.com/uk-en](https://www.rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.600 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.

## Features

|                                      |   |
|--------------------------------------|---|
| Model No.                            | RX 9360.600   |
| Design                               | universal   |
| Benefits                             | Direct mounting of moulded-case circuit-breakers (MCCBs) on the board<br>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm<br>Fast, simple pre-assembly of standard market switch types outside of the enclosure |
| Material                             | Polyamide (PA 6)<br>Fire protection corresponding to UL 94  |
| Colour                               | RAL 9005<br>RAL 35745   |
| Supply includes                      | 3 connection space covers   |
| IP protection category to IEC 60 529 | IP 2XB  |
| Rated impulse withstand voltage Uimp | 12 kV   |
| Rated voltage                        | 690 V AC<br>690 V DC<br>600 V AC (UL)   |
| Rated insulation voltage             | 1,000 V   |
| Overvoltage category                 | 4   |
| Contamination level                  | 3   |
| Number of poles                      | 3-pole  |

# Features

|                                   |   |
|-----------------------------------|---|
| Cable outlet                      | Bottom  |
| Type of electrical connection     | Box terminal  |
| To fit manufacturer (model)       | ABB (A1, S2, T1, T2, XT1, XT2, FD63/FD160)<br>BTicino (M1 160)<br>Chint (NM8N-125, NM1-63H, NM1-125H, NXM-63S, NXM-125S, NXM-160S, NXMS-160)<br>Eaton (NZM1)<br>Fuji Electric (BW125JAG-3P)<br>Hager (P160)<br>Himel (HDM3-100F/N, HDM3L-125)<br>Hyundai Electric (100AF, 125AF, 125D, 160D AF)<br>Legrand (DPX 160, DPX 250 ER, DPX <sup>3</sup> 160)<br>LS Electric (100AF, 125AF, TE100, TD100, TE160, TD160)<br>Mitsubishi (NF63-SV, NF125-SV)<br>OEZ (BC160)<br>Rockwell (140G-C2C3-D10, 140G-C2C3-D12, 140-C2E3-D16, 140G-H0F3-D10, 140G-H0F3-D12, 140G-H0F3-D16)<br>Sassin (3SM8L-100)<br>Schneider (NSC100N, NSXm50, NSXm100, NSXm160, NSXm250, NSE100)<br>Schrack (MC1)<br>Siemens (3VA10, 3VA11)<br>Terasaki (E125, S125) |
| To fit busbar system              | RiLineX<br>RiLine60   |
| Fundamental frequency             | 50...60 Hz  |
| Ambient humidity (non-condensing) | 10...90 %   |
| To fit busbars                    | 15 x 5/10<br>20 x 5/10<br>30 x 5/10   |
| Operating temperature range       | -25 °C...55 °C  |
| Storage temperature range         | -25 °C...75 °C  |
| Dimensions                        | Width: 81 mm<br>Height: 252 mm<br>Depth: 63 mm  |

# Features

|                              |               |
|------------------------------|---------------|
| Packs of                     | 1 pc(s).      |
| Net weight                   | 0.92          |
| Gross weight                 | 1.22          |
| Copper weight (kg per piece) | 0.375         |
| Customs tariff number        | 85369095      |
| EAN                          | 4028177997103 |
| ETIM 9                       | EC001531      |

# Approvals

|           |                    |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|