Rittal – The System.

Faster – better – everywhere.



SV 9665.750

Cable entry gland

State: 31/10/2026 (Source: www.rittal.com/uk-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9665.750 - Cable entry gland for roof plate

Cable entry glands for roof plates, with metric knockouts, sealing membranes, entry glands, or sealed.



Features

Model No.	SV 9665.750
Design	14 x M25/32
Product description	For simple, secure cable entry in the roof zone.
Material	Insulating material
Colour	RAL 7035
Supply includes	Seal included
No. of metric knockouts	14 x M25/M32
Dimensions	Width: 250 mm Depth: 160 mm
IP protection category to IEC 60 529	IP 55
Packs of	1 pc(s).
Net weight	0.25 kg
Gross weight	0.279 kg
Customs tariff number	39269097
ETIM 9	EC000211
ECLASS 8.0	27142421

Features

Product description	SV Cable entry gland, 14xM25/32, insulating material