

Rittal – The System.

Faster – better – everywhere.



SV 9690.040

Energy storage enclosure

State: 14/06/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9690.040 - Energy storage enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. With flexible interior fit-out. Ideal for efficient and modular energy storage installation with slide rails.

Features

| | |
|-----------------------------------|---|
| Model No. | SV 9690.040 |
| Design | With flexible interior fit-out |
| Material | Enclosure frame: Sheet steel, 1.5 mm Roof plate: Sheet steel, 1.5 mm Door: Sheet steel, 1.5 mm Rear panel: Sheet steel, 1.5 mm |
| Surface finish | Enclosure frame: Dipcoat-primed Door, roof and rear panel: Powder-coated, textured paint |
| Colour | RAL 7035 |
| Supply includes | Enclosure frame Door and rear panel, perforated Roof plate Lock: 3 mm double-bit |
| Protection category to IEC 60 529 | IP 20 |
| Dimensions | Width: 600 mm Height: 2,000 mm Depth: 600 mm |
| Packs of | 1 pc(s). |
| Net weight | 66 kg |
| Gross weight | 66.2 kg |
| PCF per pack (cradle-to-gate) | 208.2 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |

Features

Product description

VX ESS energy storage enclosure WxHxD: 600x2000x600 mm, with door, rear panel, interior fit-out

Approvals

Explanations

Declaration of conformity