

Rittal – The System.

Faster – better – everywhere.



AE 1014.600 Wall-mounted AE

State: 8/24/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1014.600 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

Features

| | |
|--------------------------------------|---|
| Model No. | AE 1014.600 |
| Material | Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4301 (AISI 304) |
| Surface finish | Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting panel: Zinc-plated |
| Supply includes | Housing with door(s) Mounting panel Lock: 3 mm double-bit |
| Protection category NEMA | NEMA 4X |
| Protection category IP to EN 60529 | IP 66 |
| IK code | IK08 |
| Dimensions | Width: 760 mm Height: 760 mm Depth: 300 mm Width: 29.9 " Height: 29.9 " Depth: 11.8 " |
| Dimensions of mounting plate (W x H) | 704 mm x 730 mm 27.7 " x 28.7 " |
| Number of doors | 1 |
| No. of locks | 2 |

Features

| | |
|-----------------------|---|
| Lock | Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit Material lock: Die-cast zinc, nickel-plated |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Packaging unit | 1 pc(s). |
| Net weight | 40.4 |
| Gross weight | 42.5 |
| Customs tariff number | 94032080 |
| EAN | 4028177000520 |
| E-Number Sweden | E3404422 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |

Approvals

| | |
|--------------|---|
| Approvals | DNV-GL Lloyds Register of Shipping UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |