Rittal – The System.

Faster – better – everywhere.



AX 1016.000

Basic enclosure AX, stainless steel

State: 11/2/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AX 1016.000 - Basic enclosure AX, stainless steel

The robust stainless steel housings feature an integrated cam system that allows for extensive system expansion without drilling, quickly and securely.







Features

Model No.	AX 1016.000
Material	Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4301 (AISI 304)
Surface finish	Enclosure and door: Brushed, grain size 400 Mounting panel: Zinc-plated
Supply includes	Housing with door(s), swing angle 130° Mounting panel Lock: 3 mm double-bit
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 4X NEMA 12
Protection category IP to EN 60 529	IP 66
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12

© Rittal 2026

Features

IK code	IK10
Dimensions	Width: 800 mm Height: 1,000 mm Depth: 300 mm Width: 31.5 ″ Height: 39.4 ″ Depth: 11.8 ″
Material thickness - door	2 mm 0.08 ″
Material thickness - enclosure	1.5 mm 0.06 ″
Material thickness – mounting plate	2.5 mm 0.1 ″
Dimensions of mounting plate (W x H)	745 mm x 975 mm 29.3 ″ x 38.4 ″
Number of doors	1
Lock	Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit Material lock: Die-cast zinc
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	50.3 kg
Gross weight	51 kg
PCF/VE (cradle-to-gate)	172.68
Customs tariff number	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	AX wall-mounted enclosure, WHD: 800x1000x300 mm, 304 stainless steel, with mounting panel, single-door, with two cam locks

Approvals

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration