


Rittal – The System.

Faster – better – everywhere.



SV 9635.045 Board

State: 12/07/2025 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.045 - Board RiLine Compact

Board with integral busbars.

Features

Model No.	SV 9635.045
Function principle	Shock-hazard-protected busbar board for the safe accommodation and contacting of components, thanks to simple plug-in mounting Pre-punched pitch units in the board allow secure, fast positioning of components Reduces wiring work by contacting directly onto the board
Material	Polyamide Polycarbonate E-Cu Fire protection corresponding to UL 94
Colour	RAL 7035
Supply includes	Integral busbars
IP protection category to IEC 60529	IP 2X
Standards	UL 508 IEC 61 439
Rated current max.	160 A
Rated operating voltage	690 V (AC) 600 V (DC)
Note	The technical data may vary for UL applications
for mounting plate assembly	Yes
Number of poles	3-pole
Dimensions	Width: 1,000 mm Height: 160 mm Depth: 45.1 mm
Packs of	1 pc(s).
Net weight	3.91

Features

Gross weight	4.06
Copper weight (kg per piece)	2.24
Customs tariff number	85469010
EAN	4028177978393
ETIM 9	EC001900
ETIM 8	EC001900
ECLASS 8.0	27400613

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------