

# Rittal – The System.

Faster – better – everywhere.



## SV 9635.300 Component adaptor

State: 12/05/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9635.300 - Component adaptor 3-pole

For assembly of switchgear and protective gear.

## Features

|                            |  |
|----------------------------|--|
| Model No.                  | SV 9635.300  |
| Design                     | With integral fuse holder  |
| Function principle         | For mechanical attachment and direct contacting of electrical equipment on the board |
| Material                   | Polyamide<br>Fire protection corresponding to UL 94                                  |
| Colour                     | RAL 7035   |
| Note                       | The technical data may vary for UL applications                                      |
| Rated current max.         | 16 A   |
| Rated operating voltage    | 690 V (AC)<br>600 V (DC)   |
| Number of poles            | 3-pole   |
| For fuse type (class)      | CC   |
| Electrical ratings UL      | Rated operating voltage (max.) UL: 600 V AC  |
| Connection cables (AWG)    | AWG 14   |
| Length of connection cable | 125 mm   |
| Support rails Qty/height   | 1 / 10 mm  |
| Support rail type          | static   |
| Dimensions                 | Width: 22.5 mm<br>Height: 160 mm<br>Depth: 80 mm                                     |
| Packs of                   | 1 pc(s).   |
| Net weight                 | 0.124 kg   |
| Gross weight               | 0.134 kg   |

# Features

---

|                              |  |
|------------------------------|--|
| Copper weight (kg per piece) | 0.02   |
| Customs tariff number        | 85369095   |
| ETIM 9                       | EC001531   |
| ECLASS 8.0                   | 27370304   |
| Product description          | SV Component adaptor, 16 A, 690 V (AC), 600 V (DC), 3-pole, for fuse 10x38 mm/Class CC, connection cable AWG 14 (L: 125 mm), WH: 22,5x160 mm |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |