



# Rittal – The System.

Faster – better – everywhere.



## SV 9635.410

## Motor controller

State: 15/01/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))



# SV 9635.410 - Motor controller 3-pole

For controlling motors as direct or reversing starters with integral over-ride protection

## Features

Model No.	SV 9635.410
Function principle	<p>For controlling motors as direct or reversing starters with integral over-ride protection</p> <p>The hybrid technology used facilitates frequent switching by semiconductors with zero wear</p> <p>During operation, mechanical contacts ensure a low heat loss</p> <p>Space-saving configuration thanks to the minimal build width</p>
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Power dissipation (max.)	5.5 W
Rated operating voltage	500 V (AC), 3~, 50 Hz/60 Hz
Rated current max.	2.4 A
Note	The technical data may vary for UL applications
Dimensions	Width: 22.5 mm Height: 160 mm Depth: 114 mm
Connection of round conductors	0.14 - 2.5 mm <sup>2</sup>
Adjustable current monitoring	0.18 - 2.4 A
Packs of	1 pc(s).
Net weight	0.38
Gross weight	0.387
Customs tariff number	85371091
EAN	4028177817302
ETIM 9	EC002572

# Features

## ECLASS 8.0

27370804

# Approvals

Approvals UL + C-UL (listed)

## Explanations Declaration of conformity