

Rittal – The System.

Faster – better – everywhere.



VX 9666.956

Bayed enclosure system VX25

State: 18/04/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 9666.956 - Bayed enclosure system VX25 Distribution enclosure

Baying systems VX as distribution enclosures, prepared for ISV installation modules



Features

| | |
|-----------------|--|
| Model No. | VX 9666.956 |
| Material | Sheet steel |
| Surface finish | Enclosure frame: Dipcoat-primed Door(s), roof, rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Gland plates: Zinc-plated |
| Colour | RAL 7035 |
| Supply includes | Enclosure frame Door(s) Door hinged on the right, may be swapped to the left Gland plates Rear panel Roof plate Lock: 3 mm double-bit |
| Number of doors | 1 |
| Note | For 600 mm wide distribution enclosures, please use VX basic enclosures For a base/plinth height of 200 mm, 2 packs each of plinth corner pieces, 100 mm and base/plinth trim panels, 100 mm are required |

Features

| | |
|-------------------------------------|--|
| IP protection category to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 12 |
| Test specification | IEC 61 439-1/-2 |
| Dimensions | Width: 850 mm Height: 2,000 mm Depth: 400 mm |
| Packs of | 1 pc(s). |
| Net weight | 84.2 kg |
| Gross weight | 85.8 kg |
| PCF per pack (cradle-to-gate) | 273.5 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000214 |
| ECLASS 8.0 | 27142409 |
| Product description | VX Distribution enclosure (ISV), WHdepth 850x2000x400 mm, sheet steel, single-door |

Approvals

| | |
|--------------|------------------------------|
| Approvals | Bureau Veritas DNV-GL |
| Certificates | Surface finish |
| Explanations | Declaration of conformity UK |