

Rittal – The System.

Faster – better – everywhere.



SV 9681.206

Perforated mounting strip

State: 23/05/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9681.206 - Perforated mounting strip for partial door

For retrospective external mounting on partial doors, with 25 mm hole pitch pattern for mounting individual items on the rear of doors such as cable ducts, conduit holders, etc.



Features

Model No.	SV 9681.206
Product description	For retrospective external mounting on partial doors. The perforated mounting strips have a 25 mm pitch pattern of holes and may be used for mounting individual accessories such as cable ducts, conduit holders etc. on the rear of the door. Hole diameter of perforated mounting strip: 4.5 mm.
Material	Sheet steel, 1 mm
Surface finish	Zinc-plated
Supply includes	Assembly parts
Length	398 mm
Assembly instruction	For 1000 mm enclosure width: 1 x 9681.204 and 1 x 9681.206 For 1200 mm enclosure width: 2 x 9681.206
Dimensions	Length: 398 mm
To fit	Width: 600 mm
OUT_SUITABLE_FOR_PARTIAL_DOOR_HEIGHTS	150 - 800 mm
Packs of	10 pc(s).
Net weight	1.2 kg
PCF per pack (cradle-to-gate)	4.9 kg CO2 eq (Cat B)

Features

Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC000386
ECLASS 8.0	27400501
Product description	SV Perforated mounting strip, L: 398 mm, for partial door WH: 600x150-800 mm

Approvals

Explanations	Declaration of conformity UK
--------------	------------------------------