Rittal - The System.

Faster – better – everywhere.





HD 1305.600 Compact enclosure HD, single-door

State: 10/30/2025 (Source: rittal.com/us-en)




HD 1305.600 - Compact enclosure HD, single-door

Enclosure solution tailored to the requirements of the food and beverage industry. Roof angled forwards by 30°. Seal dyed blue to clearly distinguish it from foodstuffs







Features

| Model No. | HD 1305.600 | |
|----------------------|--|--|
| Version | Hygienic Design Enclosures | |
| Product modification | From June 2020, the compact enclosure HD, single-door, comes with the new compact enclosure AX mounting plate. | |
| Material | Housing and door: Stainless steel 1.4301 (AISI 304) | |
| | Mounting plate: Carbon steel | |
| | HD lock inserts: Stainless steel 1.4404 (AISI 316L) | |
| | Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 | |
| Surface finish | Housing and door: Brushed, grain 400, peak-to-valley height | |
| | < 0.8 μm | |
| | Mounting panel: Zinc-plated | |
| | Seal: Blue, dyed (RAL 5010) | |
| Supply includes | Housing of all-round solid construction | |
| | Door with fitted seal | |
| | Door hinged on the right, may be swapped to the left | |
| | Mounting panel | |

© Rittal 2025 2

Features

| Dimensions | Width: 390 mm Height, front: 550 mm Height rear: 669 mm Depth: 210 mm Width: 15.4 " Height, front: 21.7 " Height rear: 26.3 " Depth: 8.27 " |
|---|--|
| Dimensions of mounting plate (W x H) | 330 mm x 475 mm 13 " x 18.7 " |
| Door opening angle | 125° |
| IK code | IK08 |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Protection category IP to IEC 60 529 | IP 66 IP X9 |
| Protection category NEMA | NEMA 1 NEMA 3 NEMA 3X NEMA 4 NEMA 4X NEMA 12 NEMA 13 |
| Type rating according to UL 50E | Type 1 Type 3 Type 3X Type 4 Type 4X Type 12 Type 13 |
| Packaging unit | 1 pc(s). |
| Net weight | 15 |
| Gross weight | 17 |
| Customs tariff number | 94032080 |
| EAN | 4028177967458 |

© Rittal 2025 3

Features

| ETIM 9 | EC000261 | |
|------------|----------|--|
| ETIM 8 | EC000261 | |
| ECLASS 8.0 | 27180101 | |

Approvals

| Approvals | UL + C-UL (listed) |
|--------------|------------------------------|
| Explanations | Declaration of conformity |
| | Declaration of conformity UK |

© Rittal 2025