

Rittal – The System.

Faster – better – everywhere.



HD 1319.600 Two-door HD Enclosure

State: 4/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 1319.600 - Two-door HD Enclosure

Enclosure solution tailored to the requirements of the food and beverage industry. Roof angled forwards by 30°. Seal dyed blue to clearly distinguish it from foodstuffs



Features

Model No.	HD 1319.600
Version	Hygienic Design Enclosures
Material	Enclosure and doors: stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel HD lock inserts: Stainless steel 1.4404 (AISI 316L) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting panel: Zinc-plated Seal: Blue, dyed (RAL 5010)
Supply includes	Housing of all-round solid construction Doors with fitted seal Mounting panel

Features

Dimensions	Width: 1,010 mm Height, front: 1,250 mm Height rear: 1,480 mm Depth: 400 mm Width: 39.8 " Height, front: 49.2 " Height rear: 58.3 " Depth: 15.7 "
Dimensions of mounting plate (W x H)	945 mm x 1,175 mm 37.2 " x 46.3 "
Door opening angle	125°
IK code	IK08
Base material	Stainless steel 1.4301 (AISI 304)
Protection category IP to IEC 60529	IP 66 IP X9
Protection category NEMA	NEMA 1 NEMA 3 NEMA 3X NEMA 4 NEMA 4X NEMA 12 NEMA 13
Type rating according to UL 50E	Type 1 Type 3 Type 3X Type 4 Type 4X Type 12 Type 13
Packaging unit	1 pc(s).
Net weight	91.2 kg
Gross weight	92.5 kg
Customs tariff number	94032080
ETIM 9	EC000261

Features

ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	HD compact enclosure, WHD: 1010x1250(H1)x1480(H2)x400 mm, stainless steel, 1.4301, with mounting plate, with hinged door and silicone seal

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK PCF-declaration