Rittal – The System.

Faster – better – everywhere.





HD 1319.600 Two-door HD Enclosure

State: 11/18/2025 (Source: rittal.com/us-en)



HD 1319.600 - Two-door HD Enclosure

Enclosure solution tailored to the requirements of the food and beverage industry. Roof angled forwards by 30°. Seal dyed blue to clearly distinguish it from foodstuffs







Features

Model No.	HD 1319.600
Version	Hygienic Design Enclosures
Material	Enclosure and doors: stainless steel 1.4301 (AISI 304)
	Mounting plate: Carbon steel
	HD lock inserts: Stainless steel 1.4404 (AISI 316L)
	Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height
	< 0.8 μm
	Mounting panel: Zinc-plated
	Seal: Blue, dyed (RAL 5010)
Supply includes	Housing of all-round solid construction
	Doors with fitted seal
	Mounting panel

© Rittal 2025

Features

Dimensions	Width: 1,010 mm Height, front: 1,250 mm Height rear: 1,480 mm Depth: 400 mm Width: 39.8 " Height, front: 49.2 " Height rear: 58.3 " Depth: 15.7 "
Dimensions of mounting plate (W x H)	945 mm x 1,175 mm 37.2 ″ x 46.3 ″
Door opening angle	125°
IK code	IK08
Base material	Stainless steel 1.4301 (AISI 304)
Protection category IP to IEC 60 529	IP 66 IP X9
Protection category NEMA	NEMA 1 NEMA 3 NEMA 3X NEMA 4 NEMA 4X NEMA 12 NEMA 13
Type rating according to UL 50E	Type 1 Type 3 Type 3X Type 4 Type 4X Type 12 Type 13
Packaging unit	1 pc(s).
Net weight	91.2
Gross weight	92.5
Customs tariff number	94032080
EAN	4028177918528

© Rittal 2025 3

Features

ETIM 9	EC000261	
ETIM 8	EC000261	
ECLASS 8.0	27180101	

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025