


Rittal – The System.

Faster – better – everywhere.



AE 1036.500

Wall-mounted AE

State: 1/31/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1036.500 - Wall-mounted AE

Housing with door of carbon steel, spray-finished with mounting plate and gland panel in the base.

Features

Model No.	AE 1036.500
Material	Housing: Carbon steel Door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with hinged door(s), of all-round solid construction Flange (gland) plate(s) in enclosure base Mounting panel Lock: 3 mm double-bit
Protection category NEMA	NEMA 4
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 300 mm Height: 300 mm Depth: 155 mm Width: 11.8 " Height: 11.8 " Depth: 6.1 "
Material thickness - door	1.5 mm 0.06 "
Material thickness - enclosure	1.38 mm 0.05 "
Material thickness – mounting plate	2 mm 0.08 "

Features

Dimensions of mounting plate (W x H)	254 mm x 275 mm 10 " x 10.8 "
Number of doors	1
Interchangeable door catch	Yes
No. of locks	1
Lock	Lock version: Cam No. of locks: 1 Lock Insert: 3 mm double-bit
Gland plate	Qty.: 1
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	5.786
Gross weight	6.2
EAN	4028177522909
E-Number Sweden	E3404504
ECLASS 8.0	27180101

Approvals

Approvals	DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK
