


Rittal – The System.

Faster – better – everywhere.



KS 1467.500

KS Plastic Enclosures

State: 2/16/2026 (Source: ittal.com/us-en)



FRIEDHELM LOH GROUP

KS 1467.500 - KS Plastic Enclosures

Wall-mounted housing with door of fiberglass-reinforced, non-saturated polyester, with mounting plate. Optionally with or without glazed door. Protection category IP 56 or IP 66. Infinite mounting plate depth adjustment, thanks to multiple mounting levels in the enclosure. Flexible interior door configuration using press-fitted mounting bosses in the door. High stability thanks to use of fibre-glass reinforced plastic.



Features

| | |
|-----------------|--|
| Model No. | KS 1467.500 |
| Version | with viewing window |
| Material | Housing and door: Fiberglass-reinforced unsaturated polyester Door: All-round foamed-in PU seal Mounting plate: Carbon steel Viewing window: Glazed acrylic, 3.0 mm with all-round rubber cable clamp strip |
| Surface finish | Housing and door: Dyed plastic with no after-treatment Mounting panel: Zinc-plated |
| Color | Similar to RAL 7035 |
| Supply includes | Housing with hinged door, of all-round solid construction, 3 mm double-bit lock Mounting panel Twin seal on the top and bottom edges of the door as integral rain protection strip Press-fitted C sections at the sides for infinitely variable mounting plate depth adjustment Viewing window in the door |

Features

| | |
|--------------------------------------|---|
| Note | Under the influence of long-term UV radiation (sunlight) in conjunction with wind and rain, the surface finish may become visually impaired. This does not affect the protection of the installed electrical components in any way. If the enclosures cannot be protected from UV radiation, we recommend that they should be painted with a PUR paint. Permissible ambient temperature -30 °C... +75 °C. |
| Protection category NEMA | NEMA 12 |
| Protection category IP to EN 60 529 | IP 56 |
| IK code | IK08 |
| Dimensions | Width: 600 mm Height: 600 mm Depth: 200 mm Width: 23.6 " Height: 23.6 " Depth: 7.87 " |
| Material thickness – mounting plate | 2.5 mm 0.1 " |
| Dimensions of mounting plate (W x H) | 545 mm x 550 mm 21.5 " x 21.7 " |
| Number of doors | 1 |
| Interchangeable door catch | Yes |
| No. of locks | 2 |
| Lock | Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit |
| With viewing window | Yes |
| Base material | Plastic |
| Packaging unit | 1 pc(s). |
| Net weight | 14.768 |
| Gross weight | 15.545 |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 94037000 |
| EAN | 4028177526747 |
| E-Number Sweden | E3465010 |
| ECLASS 8.0 | 27180101 |

Approvals

| | |
|--------------|---|
| Approvals | Bureau Veritas TÜV |
| Explanations | Declaration of conformity Declaration of conformity UK |
