

Rittal – The System.

Faster – better – everywhere.



AE 1130.500 Wall-mounted AE

State: 5/9/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1130.500 - Wall-mounted AE

Housing with door of carbon steel, spray-finished with mounting plate and gland panel in the base.

Features

Model No.	AE 1130.500
Material	Housing: Carbon steel Door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with hinged door(s), of all-round solid construction Flange (gland) plate(s) in enclosure base Mounting panel Lock: 3 mm double-bit
Protection category NEMA	NEMA 12
Protection category IP to EN 60529	IP 55
IK code	IK08
Dimensions	Width: 1,000 mm Height: 760 mm Depth: 300 mm Width: 39.4 " Height: 29.9 " Depth: 11.8 "
Material thickness - door	2 mm 0.08 "
Material thickness - enclosure	1.5 mm 0.06 "
Material thickness – mounting plate	3 mm 0.12 "

Features

Dimensions of mounting plate (W x H)	944 mm x 730 mm 37.2 " x 28.7 "
Number of doors	2
No. of locks	2
Lock	Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit
Gland plate	Size: 4 Qty.: 2
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	51.1
Gross weight	54.5
Customs tariff number	94032080
EAN	4028177252417
E-Number Sweden	E3404622
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK