

Rittal – The System.

Faster – better – everywhere.



KX 1301.000

E-box KX

State: 9/6/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1301.000 - E-box KX Stainless steel

The E-Box KX, stainless steel offers remarkable ease of assembly and flexibility when selecting lock systems. The standard 180° hinges provide easy access to the enclosure interior.



Features

Model No.	KX 1301.000
Product description	The small enclosure KX, E-Box KX, stainless steel offers remarkable ease of assembly and flexibility when selecting lock systems. The standard 180° hinges provide easy access to the enclosure interior.
Material	Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4404 (AISI 316L)
Surface finish	Housing and cover: Brushed, grain 180 Mounting panel: Zinc-plated
Supply includes	Mounting panel Cam lock with 3 mm double-bit insert
Protection category IP to EN 60529	IP 66
Type rating according to UL 50E	Type 1 Type 3R Type 3RX Type 4 Type 4X Type 12

Features

Dimensions	Width: 200 mm Height: 300 mm Depth: 155 mm Width: 7.87 " Height: 11.8 " Depth: 6.1 "
Dimensions of mounting plate (W x H)	175 mm x 275 mm 6.89 " x 10.8 "
Material thickness - enclosure	1.25 mm 0.05 "
Material thickness - door	1.25 mm 0.05 "
Lock	No. of locks: 1
Base material	Stainless steel 1.4404 (AISI 316L)
Packaging unit	1 pc(s).
Net weight	3.88
Gross weight	3.889
Customs tariff number	94032080
EAN	4028177919037
E-Number Sweden	E3465169
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
-----------	---

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK