Rittal – The System.

Faster – better – everywhere.



KX 1301.000

E-box KX

State: 11/10/2026 (Source: www.rittal.com/us-en)

KX 1301.000 - E-box KX Stainless steel

The E-Box KX, stainless steel offers remarkable ease of assembly and flexibility when selecting lock systems. The standard 180° hinges provide easy access to the enclosure interior.







Features

Model No.	KX 1301.000
Product description	The small enclosure KX, E-Box KX, stainless steel offers remarkable ease of assembly and flexibility when selecting lock systems. The standard 180° hinges provide easy access to the enclosure interior.
Material	Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4404 (AISI 316L)
Surface finish	Housing and cover: Brushed, grain 180 Mounting panel: Zinc-plated
Supply includes	Mounting panel Cam lock with 3 mm double-bit insert
Dimensions	Width: 200 mm Height: 300 mm Depth: 155 mm Width: 7.87 ″ Height: 11.8 ″ Depth: 6.1 ″
Dimensions of mounting plate (W x H)	175 mm x 285 mm 6.89 ″ x 11.2 ″
Protection category IP to EN 60 529	IP 66

© Rittal 2026

Features

Type rating according to 508A	Type 1 Type 3R Type 3RX Type 4 Type 4X Type 12
Material thickness - enclosure	1.25 mm 0.05 ″
Material thickness - door	1.25 mm 0.05 ″
Lock	No. of locks: 1 Material lock: Stainless steel 1.4404 (AISI 316L)
Base material	Stainless steel 1.4404 (AISI 316L)
Packaging unit	1 pc(s).
Net weight	3.88 kg
Gross weight	3.889 kg
PCF/VE (cradle-to-gate)	13.5
Customs tariff number	84879059
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	KX E-Box, WHD: 200x300x155 mm, stainless steel 1.4401, with mounting plate, single-door, with cam lock

Approvals

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)

Approvals

Explanations	Declaration of conformity PCF-declaration