

# Rittal – The System.

Faster – better – everywhere.



## HD 1306.600

### Compact enclosure HD, single-door

State: 2/1/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# HD 1306.600 - Compact enclosure HD, single-door

Enclosure solution tailored to the requirements of the food and beverage industry. Roof angled forwards by 30°. Seal dyed blue to clearly distinguish it from foodstuffs



## Features

Model No.	HD 1306.600
Version	Hygienic Design Enclosures
Product modification	From June 2020, the compact enclosure HD, single-door, comes with the new compact enclosure AX mounting plate.
Material	Housing and door: Stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel HD lock inserts: Stainless steel 1.4404 (AISI 316L) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting panel: Zinc-plated Seal: Blue, dyed (RAL 5010)
Supply includes	Housing of all-round solid construction Door with fitted seal Door hinged on the right, may be swapped to the left Mounting panel

# Features

Dimensions	Width: 390 mm Height, front: 430 mm Height rear: 549 mm Depth: 210 mm Width: 15.4 " Height, front: 16.9 " Height rear: 21.6 " Depth: 8.27 "
Dimensions of mounting plate (W x H)	330 mm x 355 mm 13 " x 14 "
Door opening angle	125°
No. of locks	2
IK code	IK08
Base material	Stainless steel 1.4301 (AISI 304)
Protection category IP to IEC 60529	IP 66 IP X9
Protection category NEMA	NEMA 1 NEMA 3 NEMA 3X NEMA 4 NEMA 4X NEMA 12 NEMA 13
Type rating according to UL 50E	Type 1 Type 3 Type 3X Type 4 Type 4X Type 12 Type 13
Packaging unit	1 pc(s).
Net weight	12.9
Gross weight	13.1
Customs tariff number	94032080

# Features

---

EAN	4028177567603
E-Number Sweden	E3465017
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

---

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

---