Rittal – The System.

Faster - better - everywhere.





EB 1554.500 E-Box EB

State: 11/6/2025 (Source: rittal.com/us-en)



EB 1554.500 - E-Box EB

Wall-mounted housing with door and mounting plate made from sheet steel. Protection category IP 66. With 180° hinge. Lock insert may be exchanged for individual lock systems.

Features

Model No.	EB 1554.500
Material	Housing and door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with hinged door 180° hinge Cam lock with 3 mm double-bit insert Mounting panel
Protection category NEMA	NEMA 4
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 200 mm Height: 300 mm Depth: 120 mm Width: 7.87 " Height: 11.8 " Depth: 4.72 "
Dimensions of mounting plate (W x H)	175 mm x 285 mm 6.89 ″ x 11.2 ″
Material thickness - enclosure	1.25 mm 0.05 ″
Material thickness - door	1.25 mm 0.05 ″

© Rittal 2025

Features

Material thickness - mounting	2 mm
plate	0.08 ″
Lock	Lock version: Cam
	No. of locks: 1
	Lock Insert: 3 mm double-bit
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	3.361
Gross weight	3.561
Customs tariff number	94032080
EAN	4028177251724
E-Number Sweden	E3404649
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas
	C-UL
	Lloyds Register of Shipping
	UL
	UL + C-UL (listed)
Explanations	Manufacturer's declaration
	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3