


# Rittal – The System.

Faster – better – everywhere.



## KX 1560.000 KX terminal box

State: 7/20/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KX 1560.000 - KX terminal box Stainless steel

The KX small enclosure stainless steel offers maximum data quality and consistency in engineering, flexibility, and safety for a variety of applications.



## Features

Model No.	KX 1560.000
Product description	System perfection. The new small enclosure KX, stainless steel offers maximum data quality and consistency in engineering, flexibility, and safety for a variety of applications.
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Housing and cover: Brushed, grain 180
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 1 NEMA 3R NEMA 3RX NEMA 4 NEMA 4X NEMA 12
Protection category IP to EN 60529	IP 66

# Features

Type rating according to UL 50E	Type 1 Type 3R Type 3RX Type 4 Type 4X Type 12
Dimensions	Width: 150 mm Height: 150 mm Depth: 80 mm Width: 5.91 " Height: 5.91 " Depth: 3.15 "
Material thickness - cover	1.25 mm 0.05 "
Material thickness - enclosure	1.5 mm 0.06 "
Lock	No. of locks: 4
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	1.12
Gross weight	1.323
Customs tariff number	84879090
EAN	4028177919174
E-Number Sweden	E3465226
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

## Approvals

# Approvals

---

## Approvals

Bureau Veritas  
DNV-GL  
Lloyds Register of Shipping  
UL + C-UL (listed)

---

## Explanations

Declaration of conformity  
Declaration of conformity UK