Rittal – The System.

Faster – better – everywhere.





KX 1566.000 KX terminal box

State: 11/6/2025 (Source: rittal.com/us-en)



KX 1566.000 - KX terminal box Stainless steel

The KX small enclosure stainless steel offers maximum data quality and consistency in engineering, flexibility, and safety for a variety of applications.







Features

| Model No. | KX 1566.000 |
|--|---|
| Product description | System perfection. The new small enclosure KX, stainless steel offers maximum data quality and consistency in engineering, flexibility, and safety for a variety of applications. |
| Material | Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal |
| Surface finish | Housing and cover: Brushed, grain 180 |
| Supply includes | Housing with cover Quick-release fasteners including plastic bushings |
| Protection category NEMA | NEMA 1 NEMA 3R NEMA 3RX NEMA 4 NEMA 4X NEMA 12 |
| Protection category IP to EN 60 529 | IP 66 |

© Rittal 2025

Features

| Type rating according to UL 50E | Type 1 |
|---------------------------------|-----------------------------------|
| | Type 3R |
| | Type 3RX |
| | Type 4 |
| | Type 4X |
| | Type 12 |
| Dimensions | Width: 300 mm |
| | Height: 200 mm |
| | Depth: 120 mm |
| | Width: 11.8 " |
| | Height: 7.87 " |
| | Depth: 4.72 " |
| Material thickness - cover | 1.25 mm |
| | 0.05 ″ |
| Material thickness - enclosure | 1.25 mm |
| | 0.05 ″ |
| Lock | No. of locks: 4 |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Packaging unit | 1 pc(s). |
| Net weight | 2.7 |
| Gross weight | 2.866 |
| Customs tariff number | 84879059 |
| EAN | 4028177919204 |
| E-Number Sweden | E3465232 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| | |

Approvals

© Rittal 2025 3

Approvals

| Approvals | Bureau Veritas |
|--------------|-----------------------------|
| | DNV-GL |
| | Lloyds Register of Shipping |
| | UL + C-UL (listed) |
| Explanations | Declaration of conformity |

© Rittal 2025 4