

Rittal – The System.

Faster – better – everywhere.



KX 1579.000

E-box KX, carbon steel

State: 2/8/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))



FRIEDHELM LOH GROUP

KX 1579.000 - E-box KX, carbon steel

The small enclosure KX, E-Box KX, carbon steel offers remarkable ease of assembly and flexibility when selecting lock systems.



Features

Model No.	KX 1579.000
Product description	The small enclosure KX, E-Box KX, carbon steel offers remarkable ease of assembly and flexibility when selecting lock systems.
Material	Housing: Carbon steel Door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door Mounting panel Cam lock with 3 mm double-bit insert 180° hinge
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Protection category IP to EN 60 529	IP 66

Features

Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 12
IK code	IK08
Dimensions	Width: 300 mm Height: 800 mm Depth: 155 mm Width: 11.8 " Height: 31.5 " Depth: 6.1 "
Dimensions of mounting plate (W x H)	275 mm x 785 mm 10.8 " x 30.9 "
Material thickness - enclosure	1.25 mm 0.05 "
Material thickness - door	1.25 mm 0.05 "
Material thickness – mounting plate	2 mm 0.08 "
Lock	No. of locks: 2
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	12.287
Gross weight	12.98
PCF/VE (cradle-to-gate)	41.4 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	84879059
EAN	4028177816657
E-Number Sweden	E3465241
ETIM 9	EC000261

Features

ETIM 8 EC000261

ECLASS 8.0 27180101

Approvals

Approvals	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Certificates	Protection category
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK PCF-declaration
