Rittal - The System.

Faster – better – everywhere.





KX 1584.000 E-box KX

State: 11/8/2025 (Source: rittal.com/us-en)



KX 1584.000 - E-box KX Stainless steel

The E-Box KX, stainless steel offers remarkable ease of assembly and flexibility when selecting lock systems. The standard 180° hinges provide easy access to the enclosure interior.







Features

Model No.	KX 1584.000	
Product description	The small enclosure KX, E-Box KX, stainless steel offers remark ease of assembly and flexibility when selecting lock systems. I standard 180° hinges provide easy access to the enclosure into	
Material	Housing: Stainless steel	
	Door: Stainless steel, all-round foamed-in PU seal	
	Mounting plate: Carbon steel	
	Stainless steel 1.4301 (AISI 304)	
Surface finish	Housing and cover: Brushed, grain 180	
	Mounting panel: Zinc-plated	
Supply includes	Mounting panel	
	Cam lock with 3 mm double-bit insert	
Protection category IP to EN 60 529	IP 66	
Type rating according to UL 50E	Type 1	
	Type 3R	
	Type 3RX	
	Type 4	
	Type 4X	
	Type 12	

© Rittal 2025 2

Features

Dimensions	Width: 200 mm
	Height: 300 mm
	Depth: 120 mm
	Width: 7.87 "
	Height: 11.8 ″
	Depth: 4.72 "
Dimensions of mounting plate (W	175 mm x 275 mm
x H)	6.89 ″ x 10.8 ″
Material thickness - enclosure	1.25 mm
	0.05 ″
Material thickness - door	1.25 mm
	0.05 ″
Lock	No. of locks: 1
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	3.55
Gross weight	3.556
Customs tariff number	84879059
EAN	4028177919105
E-Number Sweden	E3465242
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas	
	DNV-GL	
	Lloyds Register of Shipping	
	UL + C-UL (listed)	

© Rittal 2025 3

Approvals

Explanations

Declaration of conformity

© Rittal 2025